CO15582

Base Product



CommScope Cat 6A, UTP, Outdoor Patch Cord

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Twisted pair patch cord

Product Series CO

Ordering Note Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but

due to their limited length are not guaranteed to meet component compliance

requirements that were developed to assess the quality of longer cords | Cords > 1 m are authorized for use in channels and are an effective standalone method used to

connect active devices

General Specifications

ANSI/TIA Category 6A

Cable Type U/UTP (unshielded)

Conductor Type Solid

Interface, Connector ARJ45 plugInterface Feature, connector AStandardInterface, Connector BRJ45 plugInterface Feature, connector BStandardJacket ColorBlack

Pairs, quantity 4

Transmission Standards IEEE 802.3bt Type 4

Wiring T568B

Dimensions

Cable Assembly Length Range (m) 1 - 100

Cable Assembly Length Range (ft) 1 - 328

Diameter Over Jacket 7.24 mm | 0.285 in

COMMSCOPE®

CO15582

Compatible Conductor Gauge, solid

24 AWG


Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

Electrical Specifications

dc Resistance, maximum0.3 ohmSafety Voltage Rating300 V

Ordering Tree



MOU

11		Foot
	М	Meter
	N	Inch
	С	Centimeter

Length

12 XXX

Notes

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

COMMSCOPE®

CO15582

Material Specifications

Contact Plating Material Gold in remating area | Nickel underplating

Jacket Material Low Smoke Zero Halogen (LSZH)

Material Type Phosphor Bronze | Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Retention Force, minimum 133 N | 29.9 lbf

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Environmental Space Outdoor
Flammability Rating CM-LS

Safety Standard ETL | cETL

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

