# SG114-12B2U



#### SureGround® Grounding Kit for 1-1/4 in coaxial cable

## Product Classification

| Product Type  | Grounding kit                   |
|---------------|---------------------------------|
| Product Brand | SureGround®                     |
| Ordering Note | CommScope® non-standard product |

## General Specifications

| Bonding Conductor Jacketing Material | PVC                        |
|--------------------------------------|----------------------------|
| Bonding Conductor Material           | Copper                     |
| Bonding Conductor Wire Size          | 6 gauge                    |
| Cable Type                           | Corrugated   Smoothwall    |
| Color                                | Black                      |
| Grounding Kit Type                   | SureGround® Grounding Kits |
| Grounding Strap Material             | Tinned copper              |
| Lug Attachment                       | Field attached             |
| Lug Type                             | Two-hole lug               |
| Thread Size                          | 3/8 in                     |

#### Dimensions

| Bonding Conductor Length                | 1,219.2 mm   48 in  |
|---|---------------------|
| Cable Jacketing Removal Length, maximum | 38.1 mm   1.5 in    |
| Cable Jacketing Removal Length, minimum | 38.1 mm   1.5 in    |
| Compatible Diameter, maximum            | 40.132 mm   1.58 in |
| Compatible Diameter, minimum            | 38.354 mm   1.51 in |
| Nominal Size                            | 1-1/4 in            |

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 5, 2023



# SG114-12B2U

## **Electrical Specifications**

| Current Handling                             | Tested to withstand 100,000 amps peak current surge |
|--|---|
| Current Handling Test Method                 | MIL-STD-1757  |
| Grounding, Bonding and Shielding Test Method | MIL-STD-188-124A                                    |
| Lightning Protection Test Method             | IEC 1024-1  |
| Material Specifications                      |   |

| Locking Bail Material | Stainless steel |
|-----------------------|-----------------|
| Rivet Material        | Tinned copper   |

### **Environmental Specifications**

| Operating Temperature           | -40 °C to +85 °C (-40 °F to +185 °F) |
|---------------------------------|--------------------------------------|
| Storage Temperature             | -40 °C to +80 °C (-40 °F to +176 °F) |
| Blowing Rain Test Method        | MIL-STD-810, Method 506              |
| Corrosion Test Method           | MIL-STD-1344, Method 1001            |
| Freezing Rain/Icing Test Method | MIL-STD-810, Method 521              |
| Humidity Test Method            | MIL-STD-1344, Method 1002            |
| Immersion Test Method           | IEC 60529:2001, IP68                 |
| UV Resistance Test Method       | MIL-STD-810, Method 505              |
| Vibration Test Method           | MIL-STD-202, Method 214              |
| Weatherproofing Method          | Butyl and electric tape              |
| Packaging and Weights           |                                      |
| Height, packed                  | 292.1 mm   11.5 in                   |
| Width nacked                    | 55.88 mm   2.2 in                    |

| 55.88 mm   2.2 in  |
|--|
| 177.8 mm   7 in  |
| Grounding kit   Hardware   Lug   One roll of 2 in PVC tape   One roll of 24 in butyl rubber tape |
| 1  |
| 0.62 kg   1.367 lb   |
|  |

# Regulatory Compliance/Certifications

Classification

Agency

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 5, 2023



# SG114-12B2U

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant

#### Included Products

42615-10 - Butyl Rubber Tape, 24 in - Black 2 in PVC Tape, 20 ft 9905-71

#### \* Footnotes

ROHS

**UK-ROHS** 

| Grounding, Bonding and Shielding Test Method | Military Standard for Grounding, Bonding, and Shielding: Bond Resistance<br>Requirement of a Maximum dc resistance of 0.001 ohm |
|--|---|
| Lightning Protection Test Method             | Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02                                  |

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: December 5, 2023

