## SG78-12B2U



#### SureGround® Grounding Kit for 7/8 in coaxial cable

#### Product Classification

| Product Type  | Grounding kit                        |
|---------------|--------------------------------------|
| Product Brand | SureGround®                          |
| Ordering Note | CommScope® standard product (Global) |

#### General Specifications

| Bonding Conductor Jacketing Material | PVC                        |
|--------------------------------------|----------------------------|
| Bonding Conductor Material           | Copper                     |
| Bonding Conductor Wire Size          | 6 gauge                    |
| Cable Type                           | Corrugated   Smoothwall    |
| Color                                | Black                      |
| Grounding Kit Type                   | SureGround® Grounding Kits |
| Grounding Strap Material             | Tinned copper              |
| Lug Attachment                       | Field attached             |
| Lug Type                             | Two-hole lug               |
| Thread Size                          | 3/8 in   M10               |

#### Dimensions

| Bonding Conductor Length                | 1,219.2 mm   48 in  |
|---|---------------------|
| Cable Jacketing Removal Length, maximum | 38.1 mm   1.5 in    |
| Cable Jacketing Removal Length, minimum | 38.1 mm   1.5 in    |
| Compatible Diameter, maximum            | 28.702 mm   1.13 in |
| Compatible Diameter, minimum            | 26.67 mm   1.05 in  |
| Nominal Size                            | 7/8 in              |

Page 1 of 7



# SG78-12B2U

#### **Electrical Specifications**

| Current Handling                             | Tested to withstand 100,000 amps peak current surge |
|--|---|
| Current Handling Test Method                 | MIL-STD-1757  |
| Grounding, Bonding and Shielding Test Method | MIL-STD-188-124A                                    |
| Lightning Protection Test Method             | IEC 1024-1  |
| Material Specifications                      |   |

| Locking Bail Material | Stainless steel |
|-----------------------|-----------------|
| Rivet Material        | Tinned copper   |

#### **Environmental Specifications**

| Operating Temperature           | -40 °C to +85 °C (-40 °F to +185 °F) |
|---------------------------------|--------------------------------------|
| Storage Temperature             | -40 °C to +80 °C (-40 °F to +176 °F) |
| Blowing Rain Test Method        | MIL-STD-810, Method 506              |
| Corrosion Test Method           | MIL-STD-1344, Method 1001            |
| Freezing Rain/Icing Test Method | MIL-STD-810, Method 521              |
| Humidity Test Method            | MIL-STD-1344, Method 1002            |
| Immersion Test Method           | IEC 60529:2001, IP68                 |
| UV Resistance Test Method       | MIL-STD-810, Method 505              |
| Vibration Test Method           | MIL-STD-202, Method 214              |
| Weatherproofing Method          | Butyl and electric tape              |
| Packaging and Weights           |                                      |
| Height, packed                  | 228.6 mm   9 in                      |

| 228.6 mm   9 in   |
|---|
| 215.9 mm   8.5 in   |
| 58.42 mm   2.3 in   |
| Grounding kit   Hardware   Lug   One roll of 2 in PVC tape   One<br>roll of 24 in butyl rubber tape |
| 1   |
| 0.62 kg   1.367 lb  |
|   |

#### Regulatory Compliance/Certifications

Classification

Agency

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 2 of 7



# SG78-12B2U

REACH-SVHC

ROHS

UK-ROHS

Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant

#### Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-71 - Black 2 in PVC Tape, 20 ft

#### \* Footnotes

| Grounding, Bonding and Shielding Test Method | Military Standard for Grounding, Bonding, and Shielding: Bond Resistance<br>Requirement of a Maximum dc resistance of 0.001 ohm |
|--|---|
| Lightning Protection Test Method             | Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02                                  |

Page 3 of 7



# 42615-10



Product Classification

#### Butyl Rubber Tape, 24 in

| Weatherproofing tape  |
|---|
| CommScope® non-standard product   |
|   |
| Provides additional moisture seal for cable connections   |
| One 1/2 in-2-1/4 in   One 1/2 in-7/8 in   One 1/2 in-7/8 in to device   Two 1/2 in-1/2 in   |
| Black   |
|   |
| 63.5 mm   2.5 in  |
| 609.6 mm   24 in  |
| 1-1/4 in   1-5/8 in   1/2 in   1/4 in   2-1/4 in   3/8 in   5/8 in   7<br>/8 in   |
|   |
| Butyl rubber tape   |
|   |
| Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 $^\circ\mathrm{F}$ then 4 hours of condensation at 104 $^\circ\mathrm{F}$ |
| ≥1000 hours   |
| 04AS00-03.6.0   MIL-STD-1344A, Method 1002  |
|   |
|   |
| 63.5 mm   2.5 in  |
| 63.5 mm   2.5 in<br>71.12 mm   2.8 in   |
|   |

Page 4 of 7



## 42615-10

Packaging quantity

1

Weight, gross

0.17 kg | 0.375 lb

### Regulatory Compliance/Certifications

Classification

#### Agency

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 5 of 7



# 9905-71



Product Classification

#### Black 2 in PVC Tape, 20 ft

| PIUUULI LIASSIIILALIUII        |  |
|--------------------------------|--|
| Product Type                   | Weatherproofing tape   |
| Ordering Note                  | CommScope® non-standard product  |
| General Specifications         |  |
| Application                    | Provides additional moisture seal for cable connections  |
| Applications per Kit           | Four 1/2 in–1/2 in   Four 1/2 in–7/8 in to device   One 1/2 in–2-1/4 in   Two 1/2 in–7/8<br>in |
| Color                          | Black  |
| Dimensions                     |  |
| Width                          | 50.8 mm   2 in   |
| Length                         | 6096 mm   240 in   |
| Nominal Size                   | 1-1/4 in   1-5/8 in   1/2 in   1/4 in   2-1/4 in   3/8 in   5/8 in   7/8 in                    |
| Material Specifications        |  |
| Material Type                  | PVC tape   |
|                                |  |
| Environmental Specification    | วกร  |
| UV Resistance Test Method      | PVC tape test method UL 510, ASTM D1000  |
| Weather Resistance Test Method | 04AS00-03.6.0   MIL-STD-1344A, Method 1002   |
| Packaging and Weights          |  |
| Height, packed                 | 63.5 mm   2.5 in   |
| Width, packed                  | 63.5 mm   2.5 in   |
| Length, packed                 | 50.8 mm   2 in   |
| Packaging quantity             | 1  |
| Weight, gross                  | 0.08 kg   0.176 lb   |
|                                |  |

Page 6 of 7



### Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 7 of 7

