

# L6CLICK

---



## Double Click-on Hanger for 1-1/4 in coaxial cable

### Product Classification

<b>Product Type</b>	Hanger kit
<b>Ordering Note</b>	CommScope® non-standard product

### General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Click-on hanger
<b>Mounting</b>	3/8 in (M10) drilled cable ladder

### Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	51.1 mm   2.012 in
<b>Width</b>	70.1 mm   2.76 in
<b>Length</b>	133.1 mm   5.24 in
<b>Compatible Cable Diameter Range</b>	38.1–40.1 mm
<b>Compatible Diameter, maximum</b>	40.1 mm   1.579 in
<b>Compatible Diameter, minimum</b>	38.1 mm   1.5 in
<b>Nominal Size</b>	1-1/4 in

### Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

### Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

# L6CLICK

---

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 37.7 cm | 14.843 in

**Width, packed** 13.9 cm | 5.472 in

**Length, packed** 15 cm | 5.906 in

**Packaging quantity** 10

**Weight, gross** 1.34 kg | 2.954 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power