



### **Product Classification**

**Product Type** Grounding kit **Product Brand** SureGround®

**Ordering Note** CommScope® non-standard product

### General Specifications

**Bonding Conductor Jacketing Material** PVC **Bonding Conductor Material** Copper **Bonding Conductor Wire Size** 6 gauge

Cable Type Corrugated | Smoothwall

Color Black

**Grounding Kit Type** SureGround® Grounding Kits

**Grounding Strap Material** Tinned copper **Lug Attachment** Factory attached Two-hole lug **Lug Type** 

Thread Size 3/8 in

#### Dimensions

**Bonding Conductor Length** 609.6 mm | 24 in Cable Jacketing Removal Length, maximum 38.1 mm | 1.5 in Cable Jacketing Removal Length, minimum 38.1 mm | 1.5 in Compatible Diameter, maximum 50.8 mm | 2 in

Compatible Diameter, minimum 49.022 mm | 1.93 in

**Nominal Size** 1-5/8 in



# SG158-06B2A

### **Electrical Specifications**

**Current Handling** Tested to withstand 100,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

Grounding, Bonding and Shielding Test Method MIL-STD-188-124A

**Lightning Protection Test Method**IEC 1024-1

Material Specifications

Locking Bail MaterialStainless steelRivet MaterialTinned copper

## **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+80 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+176 \,^{\circ}\text{F}$ )

Blowing Rain Test MethodMIL-STD-810, Method 506Corrosion Test MethodMIL-STD-1344, Method 1001Freezing Rain/Icing Test MethodMIL-STD-810, Method 521

**Humidity Test Method** MIL-STD-1344, Method 1002

Immersion Test Method IEC 60529:2001, IP68

UV Resistance Test Method MIL-STD-810, Method 505
Vibration Test Method MIL-STD-202, Method 214
Weatherproofing Method Butyl and electric tape

Packaging and Weights

 Height, packed
 304.8 mm | 12 in

 Width, packed
 279.4 mm | 11 in

 Length, packed
 25.4 mm | 1 in

Included Grounding kit | Hardware | Lug | One roll of 2 in PVC tape | One

roll of 24 in butyl rubber tape

Packaging quantity

**Weight, gross** 0.9 kg | 1.984 lb

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

# SG158-06B2A

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-71 - Black 2 in PVC Tape, 20 ft

#### \* Footnotes

Grounding, Bonding and Shielding Test Method Military Standard for Grounding, Bonding, and Shielding: Bond Resistance

Requirement of a Maximum dc resistance of 0.001 ohm

**Lightning Protection Test Method**Protection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02





### Butyl Rubber Tape, 24 in

#### **Product Classification**

Product Type Weatherproofing tape

Ordering Note CommScope® non-standard product

General Specifications

**Application** Provides additional moisture seal for cable connections

**Applications per Kit**One 1/2 in-2-1/4 in | One 1/2 in-7/8 in | One 1/2 in-7/8 in to

device | Two 1/2 in-1/2 in

**Color** Black

**Dimensions** 

 Width
 63.5 mm | 2.5 in

 Length
 609.6 mm | 24 in

**Nominal Size** 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7

/8 in

Material Specifications

Material Type Butyl rubber tape

**Environmental Specifications** 

**UV Resistance Test Method**Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4

hours of condensation at 104 °F

**UV Resistance, minimum with no degradation** ≥1000 hours

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

 Height, packed
 63.5 mm | 2.5 in

 Width, packed
 71.12 mm | 2.8 in

 Length, packed
 25.4 mm | 1 in

Page 4 of 7

**Packaging quantity** 

1

Weight, gross

0.17 kg | 0.375 lb

## Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system





#### Black 2 in PVC Tape, 20 ft

#### **Product Classification**

**Product Type** Weatherproofing tape

Ordering Note CommScope® non-standard product

General Specifications

**Application** Provides additional moisture seal for cable connections

**Applications per Kit** Four 1/2 in -1/2 in | Four 1/2 in -7/8 in to device | One 1/2 in -2-1/4 in | Two 1/2 in -7/8

in

**Color** Black

**Dimensions** 

 Width
 50.8 mm | 2 in

 Length
 6096 mm | 240 in

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in

Material Specifications

Material Type PVC tape

### **Environmental Specifications**

**UV Resistance Test Method** PVC tape test method UL 510, ASTM D1000

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

 Height, packed
 63.5 mm | 2.5 in

 Width, packed
 63.5 mm | 2.5 in

 Length, packed
 50.8 mm | 2 in

Packaging quantity 1

**Weight, gross** 0.08 kg | 0.176 lb

**COMMSCOPE®** 

## Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system