SG78-12B2U



SureGround® Grounding Kit for 7/8 in coaxial cable

Product Classification

Product TypeGrounding kitProduct BrandSureGround®

Ordering Note CommScope® standard product (Global)

General Specifications

Bonding Conductor Jacketing MaterialPVCBonding Conductor MaterialCopperBonding Conductor Wire Size6 gauge

Cable Type Corrugated | Smoothwall

Color Black

Grounding Kit Type SureGround® Grounding Kits

Grounding Strap MaterialTinned copperLug AttachmentField attachedLug TypeTwo-hole lugThread Size3/8 in | M10

Dimensions

Bonding Conductor Length1,219.2 mm | 48 inCable Jacketing Removal Length, maximum38.1 mm | 1.5 inCable Jacketing Removal Length, minimum38.1 mm | 1.5 inCompatible Diameter, maximum28.702 mm | 1.13 inCompatible Diameter, minimum26.67 mm | 1.05 in

Nominal Size 7/8 in



SG78-12B2U

Electrical Specifications

Current Handling Tested to withstand 100,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

Grounding, Bonding and Shielding Test Method MIL-STD-188-124A

Lightning Protection Test Method IEC 1024-1

Material Specifications

Locking Bail Material Stainless steel **Rivet Material** Tinned copper

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F) **Storage Temperature** -40 °C to +80 °C (-40 °F to +176 °F)

Blowing Rain Test Method MIL-STD-810, Method 506 Corrosion Test Method MIL-STD-1344, Method 1001

Freezing Rain/Icing Test Method MIL-STD-810, Method 521 **Humidity Test Method** MIL-STD-1344, Method 1002

Immersion Test Method IEC 60529:2001, IP68

UV Resistance Test Method MIL-STD-810, Method 505 **Vibration Test Method** MIL-STD-202, Method 214 Weatherproofing Method Butyl and electric tape

Packaging and Weights

Height, packed 228.6 mm | 9 in Width, packed 215.9 mm | 8.5 in Length, packed 58.42 mm | 2.3 in

Included Grounding kit | Hardware | Lug | One roll of 2 in PVC tape | One

roll of 24 in butyl rubber tape

Packaging quantity

0.62 kg | 1.367 lb Weight, gross

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Page 2 of 3

SG78-12B2U

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-71 - Black 2 in PVC Tape, 20 ft

* Footnotes

Grounding, Bonding and Shielding Test Method Military Standard for Grounding, Bonding, and Shielding: Bond Resistance

Requirement of a Maximum dc resistance of 0.001 ohm

Lightning Protection Test MethodProtection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02

