



## TENIO™ B6 144f Distribution closure round cable kit with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

Assembled TENIO closure designed for 144 fibre distribution closure kit for round cable with various diameters.

The kit contains a range of sealkits from 3mm to 12mm diameters and cable termination units to complete installation of feeder cable (loop-through) and various distributions cables. It also has a MOBRA bracket suitable for use with PIA chambers. Fibre trays and seal kits are pre-assembled into the closure in the factory to reduce engineering time in the field. This kit provides enough accessories to complete most jobs of this size and nature.

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	TENIO™
<b>Product Series</b>	TENIO

## General Specifications

<b>Cable Entry Drop Port Style</b>	Gel block
<b>Cable Entry Main Port Style</b>	Gel block
<b>Cable Ports Quantity, total</b>	6 multi-out ports (30 cables)
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Side latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Flash Test Valve</b>	Pre-installed
<b>Mounting</b>	Wall
<b>Network Area Type</b>	Distribution   Drop
<b>Splice Tray Included, quantity</b>	12
<b>Splice Tray Type Included</b>	12-fiber, single element
<b>Splices per Tray, quantity</b>	12
<b>Splicing Capacity, Single Fusion, maximum</b>	144

# 760256444 | TENIO-B6-144-ROUND

**Splicing Type, Supported** Single fusion

## Dimensions

**Height** 230 mm | 9.055 in  
**Width** 134 mm | 5.276 in  
**Length** 389 mm | 15.315 in  
**Main Cable Diameter, maximum** 16 mm | 0.63 in

## Material Specifications

**Material Type** Impact-resistant polymer

## Environmental Specifications

**Environmental Space** Below ground | Buried  
**Qualification Standards** IEC 61300, 2 m waterhead  
**Water Resistance** Flash test valve at 5 psi (40 kPa)

## Packaging and Weights

**Packaging quantity** 1  
**Packaging Type** Box | Carton  
**Weight, net** 1 kg | 2.205 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## Included Products

- 760244932 CTU-S – Fiber Closure Cable Termination Unit, Small for up to 7 mm diameter cables
- 760244933 CTU-L – Fiber Closure Cable Termination Unit, Large for up to 16 mm diameter cables
- 760250714 TENIO-MOBRA-TUBE-45x45 – TENIO™ Mounting bracket for arm mounting

# 760256444 | TENIO-B6-144-ROUND

---

- CV6797-000  
TENIO-SKG3-7/10 – TENIO™ Cable Gel Seal kit, 3 cable outlets, 7 to 10 mm diameter per cable outlet
- CV6799-000  
TENIO-SKG3-5/8 – TENIO™ Cable Gel Seal kit, 3 cable outlets, 5 to 8 mm diameter per cable outlet
- CV6800-000  
TENIO-B6-S12-12-V – TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, 12 pre-installed 12-fiber trays, 12 heat shrink splice protectors (SMOUV 45 mm), with test valve
- CW6616-000  
TENIO-SKG4-3/6 – TENIO™ Cable Gel Seal kit, 4 cable outlets, 3 to 6 mm diameter per cable outlet
- CW8862-000  
TENIO-SKG-DUMMY – TENIO™ Cable Gel Seal kit, dummy, no cable outlets, black



Fiber Closure Cable Termination Unit, Small for up to 7 mm diameter cables

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Cable termination bracket
<b>Product Series</b>	FIST-MSC   FOSC-MSC   TENIO

## Dimensions

<b>Single Cable Diameter, maximum</b>	7 mm   0.276 in
---------------------------------------	-----------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





Fiber Closure Cable Termination Unit, Large for up to 16 mm diameter cables

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Cable termination bracket
<b>Product Series</b>	FIST-MSC   FOOSC-MSC   TENIO

## Dimensions

<b>Single Cable Diameter, maximum</b>	16 mm   0.63 in
---------------------------------------	-----------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





TENIO™ Mounting bracket for arm mounting

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Mounting bracket
<b>Product Series</b>	TENIO

## General Specifications

<b>Application</b>	For use with TENIO Fiber closures
<b>Color</b>	Black

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





TENIO™ Cable Gel Seal kit, 3 cable outlets, 7 to 10 mm diameter per cable outlet

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Cable sealing
<b>Product Series</b>	TENIO

## General Specifications

<b>Application</b>	For use with TENIO Fiber closures
<b>Cable Capacity, maximum</b>	3
<b>Color</b>	Black

## Dimensions

<b>Single Cable Diameter, maximum</b>	10 mm   0.394 in
<b>Single Cable Diameter, minimum</b>	7 mm   0.276 in


## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant





TENIO™ Cable Gel Seal kit, 3 cable outlets, 5 to 8 mm diameter per cable outlet

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Cable sealing
<b>Product Series</b>	TENIO

## General Specifications

<b>Application</b>	For use with TENIO Fiber closures
<b>Cable Capacity, maximum</b>	3
<b>Color</b>	Black

## Dimensions

<b>Single Cable Diameter, maximum</b>	8 mm   0.315 in
<b>Single Cable Diameter, minimum</b>	5 mm   0.197 in

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---


## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant





# CV6800-000 | TENIO-B6-S12-12-V



TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, 12 pre-installed 12-fiber trays, 12 heat shrink splice protectors (SMOUV 45 mm), with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

## Product Classification

<b>Regional Availability</b>	EMEA   Latin America
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	TENIO™
<b>Product Series</b>	TENIO

## General Specifications


<b>Cable Entry Drop Port Style</b>	Gel block
<b>Cable Entry Main Port Style</b>	Gel block
<b>Cable Ports Quantity, total</b>	6 multi-out ports (30 cables)
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Side latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Flash Test Valve</b>	Pre-installed
<b>Mounting</b>	Wall
<b>Network Area Type</b>	Distribution   Drop
<b>Splice Tray Included, quantity</b>	12
<b>Splice Tray Type Included</b>	12-way, heat shrink
<b>Splices per Tray, quantity</b>	12
<b>Splicing Capacity, Single Fusion, maximum</b>	144
<b>Splicing Type, Supported</b>	Single fusion

## Dimensions

# CV6800-000 | TENIO-B6-S12-12-V

<b>Height</b>	230 mm   9.055 in
<b>Width</b>	134 mm   5.276 in
<b>Length</b>	389 mm   15.315 in
<b>Main Cable Diameter, maximum</b>	16 mm   0.63 in

## Ordering Tree



## Material Specifications

**Material Type** Impact-resistant polymer

## Environmental Specifications

**Environmental Space** Below ground | Buried

**Qualification Standards** IEC 61300, 2 m waterhead

**Water Resistance** Flash test valve at 5 psi (40 kPa)

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Box | Carton

**Weight, net** 1 kg | 2.205 lb

## Regulatory Compliance/Certifications


Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

# CV6800-000 | TENIO-B6-S12-12-V

---

REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





TENIO™ Cable Gel Seal kit, 4 cable outlets, 3 to 6 mm diameter per cable outlet

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Cable sealing
<b>Product Series</b>	TENIO

## General Specifications

<b>Application</b>	For use with TENIO Fiber closures
<b>Cable Capacity, maximum</b>	4
<b>Color</b>	Black

## Dimensions

<b>Single Cable Diameter, maximum</b>	6 mm   0.236 in
<b>Single Cable Diameter, minimum</b>	3 mm   0.118 in

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant





TENIO™ Cable Gel Seal kit, dummy, no cable outlets, black

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Cable sealing
<b>Product Series</b>	TENIO

## General Specifications

<b>Application</b>	For use with TENIO Fiber closures
<b>Color</b>	Black

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

