F-CLAMP-B2-3B



KwikClamp[™] Hanger for power & fiber cables, two 7-22 mm holes (alongside each other), triple block; includes hardware

Product Classification

Material Type

Product Type	Hanger kit	
Product Brand	KwikClamp™	
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa	
General Specifications		
Cables per Hanger	2	
Color	Black	
Hanger Type	KwikClamp™ hanger	
Mounting	3–25 mm angle iron 3–25 mm flat plate Round Member 8- 25 mm	
Dimensions		
Maximum Stack Height	3	
Height	204 mm 8.032 in	
Width	56 mm 2.205 in	
Length	46 mm 1.811 in	
Compatible Cable Diameter Range	7-22 mm	
Compatible Diameter, maximum	22 mm 0.866 in	
Compatible Diameter, minimum	7 mm 0.276 in	
Hanger Spacing, maximum	1.83 m 6.004 ft	
Electrical Specifications		
Return Loss Effect, maximum	0.1 dB	
DTF Effect, maximum	0.1 dB	
Material Specifications		

Engineered plastic | Stainless steel

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 16, 2024



F-CLAMP-B2-3B

Mechanical Specifications

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)	
Corrosion Resistance, minimum with no degredation	≥500 hours in salt spray chamber	
Environmental Strength Capability	Five times cable weight	
UV Resistance, minimum with no degradation	≥124 hours exposure in accelerated UV life chamber, testing duration 1344 hrs	

Packaging and Weights

Height, packed	15.5 cm 6.102 in
Width, packed	30.5 cm 12.008 in
Length, packed	35.5 cm 13.976 in
Included	Hardware
Packaging quantity	18
Weight, gross	5.149 kg 11.352 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 16, 2024

