

# LX1SXG08AAN



## Single Width LGX Module, CEx 5, 8 circuits, LC/APC connectors

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   China   EMEA   India   Latin America   North America
<b>Product Type</b>	Coexistence Element (CEx)
<b>Product Series</b>	LGX
<b>Government Funding</b>	Build America Buy America (BABA) compliant*

## General Specifications


<b>Circuits, quantity</b>	8
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC

## Port Configuration

Module Type	Networks/Services	Wavelengths (nm)
CEx 1	GPON/25G	1290 - 1500
	UPG	1260-1280 & 1525-1650
CEx 2	GPON/25G	1290 - 1500
	XGS-PON	1260 - 1280; 1575 - 1581
	UPG	1525-1560 & 1596-1650
CEx 3	GPON/25G	1290 - 1500
	RF	1550 - 1560
	UPG	1260-1280 & 1525-1540 & 1575-1650
CEx 4	GPON/25G	1290 - 1500
	XGS-PON	1260 - 1280 & 1575 - 1581
	NG-PON2	1524-1544 & 1596-1603
	UPG	1550-1560 & 1613-1650
CEx 5	PON (COMBI)	1260-1500nm & 1575-1581nm
	UPG	1525-1565nm & 1596-1650nm

# LX1SXG08AAN

## Block Diagram



## Optical Specifications

<b>Directivity, minimum</b>	50 dB
<b>Input Power, maximum</b>	200 mW
<b>Passband</b>	PON (COMBI): 1260-1500 nm & 1575-1581 nm   UPG: 1525-1565 nm & 1596-1650 nm
<b>Polarization Dependent Loss, maximum</b>	0.3 dB
<b>Polarization Mode Dispersion, maximum</b>	0.5 ps
<b>Insertion Loss, including connectors</b>	COM to PON: $\leq 0.8$ dB   COM to UPG: $\leq 0.6$ dB
<b>Isolation</b>	COM to PON: $\geq 30$ dB   COM to UPG: $\geq 15$ dB
<b>Return Loss, minimum</b>	50 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Relative Humidity</b>	5%–95%, non-condensing
<b>Qualification Standards</b>	IEC 61300-2-1   Telcordia GR-1209-CORE

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---