AQGRPRG7R

Base Product



Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 UPC (Non-Pinned) to MPO16 (Non-Pinned), Fiber Array Cable Assembly, 16-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber array cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Connector A, quantity

Color, boot A Black

Color, connector A Green

Connector B, quantity

Color, boot BBlackColor, connector BGreenConstruction TypeStranded

Furcation Color Yellow

Interface, Connector A MPO-16/APC Female
Interface, Connector B MPO-16/APC Female

Jacket ColorYellowPolarityMethod A

Fibers per Subunit, quantity 16

Total Fibers, quantity 16

COMMSCOPE®


AQGRPRG7R

Dimensions

Cable Assembly Length Range (m) 1 - 305

Cable Assembly Length Range (ft) 1 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products


760249691 – Fiber indoor cable, Plenum MPO Light Duty for Patchcords, 16 fiber, Singlemode G.657.A2/B2, P-016-MP-8G1-F30YL Feet jacket marking, Yellow jacket color

860661399 – Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, unpinned, green, for 3 mm

cable

Page 2 of 7

760249691 | P-016-MP-8G1-F30YL



Fiber indoor cable, Plenum MPO Light Duty for Patchcords, 16 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MP

General Specifications

Cable TypeMPO trunk cableConstruction TypeNon-armoredSubunit TypeGel-free


Jacket ColorYellowJacket MarkingFeet

Total Fiber Count 16

Dimensions

Diameter Over Jacket 3 mm | 0.118 in

Representative Image





Page 3 of 7

760249691 | P-016-MP-8G1-F30YL

Mechanical Specifications

Minimum Bend Radius, loaded45 mm | 1.772 inMinimum Bend Radius, unloaded24 mm | 0.945 inTensile Load, long term, maximum80 N | 17.985 lbfTensile Load, short term, maximum267 N | 60.024 lbf

 Compression
 3.5 N/mm | 19.986 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type G.657.A2/B2 | OS2

Environmental Specifications

Installation temperature $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Operating Temperature $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Storage Temperature $-40 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFNP (ETL) and c(ETL)
Flame Test Method NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $0 \,^{\circ}\text{C}$ to +70 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)

Page 4 of 7



760249691 | P-016-MP-8G1-F30YL

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 9.3 kg/km | 6.249 lb/kft

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



860661399



Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, unpinned, green, for 3 mm cable

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®
Product Type Fiber connector

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Female

Interface Feature Unpinned

Dimensions

Agency

Compatible Cable Diameter 3 mm | 0.118 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2
Insertion Loss, maximum 0.3 dB

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

CHINA-ROHS	Below maximum concentration value
100 0001 001 5	

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

COMMSCOPE®

860661399

ROHS UK-ROHS Compliant Compliant





COMMSCOPE®