## AQGRPRG7R

#### **Base Product**



Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 UPC (Non-Pinned) to MPO16 (Non-Pinned), Fiber Array Cable Assembly, 16-Fiber, Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber array cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Color, connector A

Connector A, quantity 1

Color, boot A Black

Connector B, quantity

Color, boot BBlackColor, connector BGreenConstruction TypeStrandedFurcation ColorYellow

 Interface, Connector A
 MPO-16/APC Female

 Interface, Connector B
 MPO-16/APC Female

Jacket ColorYellowPolarityMethod A

Fibers per Subunit, quantity 16

Total Fibers, quantity 16

Page 1 of 2




Green

# AQGRPRG7R

#### Dimensions

Cable Assembly Length Range (m) 1 - 305Cable Assembly Length Range (ft) 1 - 999

### Ordering Tree



#### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

**Fiber Mode** Singlemode

G.657.A2, TeraSPEED® Fiber Type

### **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Indoor | Plenum

#### Regulatory Compliance/Certifications

Classification Agency

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

Fiber indoor cable, Plenum MPO Light Duty for Patchcords, 16 fiber, Singlemode G.657.A2/B2, 760249691 P-016-MP-8G1-F30YL

Feet jacket marking, Yellow jacket color

Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, unpinned, green, for 3 mm 860661399

cable

