

# 760227306 | UD-2U



Ultra High Density 2U modular cassette sliding Panel, accepts (12)G2 modules or MPO panels, providing up to 144 duplex LC ports or up to 96 MPO ports

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	UD

## General Specifications

<b>Application</b>	Accepts twelve G2 modular cassettes
<b>Color</b>	Gray
<b>Intelligence Type</b>	iPatch® ready
<b>Interface, front</b>	Unloaded
<b>Rack Units</b>	2
<b>Shelf Movement</b>	Sliding

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	553.97 mm   21.81 in

## Material Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC)   Steel
----------------------	--

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
----------------------------	-----------

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	9.616 kg   21.2 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

