



NETCONNECT®

Structured Cabling Solutions Guide

EMEA/APAC/CALA Regions

COMMScope®

NETCONNECT® STRUCTURED CABLING SOLUTIONS GUIDE

EXCEPTIONAL VALUE, PROVEN RELIABILITY FROM COMMSCOPE

You're not unrealistic. You're simply looking for a reliable and affordable structured cabling solution; a single portfolio that can support a variety of enterprise applications—in-building LAN and data centre, outside plant and campus networks—both fibre and copper. You want hassle-free, and fast to deploy; something you can count on to support your network from day one and protect your IT investment well into the future. Say hello to NETCONNECT® from CommScope.

CommScope's NETCONNECT structured cabling portfolio continues to be a preferred solution for enterprises that need a reliable yet competitively priced infrastructure. With a complete range of copper and fibre solutions, NETCONNECT delivers proven performance across the enterprise. Designed for simplicity and engineered for flexibility, it meets your physical layer needs today and in the future.

Add CommScope's global research and manufacturing capabilities, product development support and 25-year warranty, and you've got everything you need to grow with confidence.

DRIVEN BY PROGRESS. DELIVERED BY EXPERIENCE.

In 2016, to bolster our industry-leading portfolio, CommScope acquired well-respected enterprise cabling brands KRONE, AMP NETCONNECT, and ADC and consolidated them into **one NETCONNECT** brand. Our forty years of proven experience means we can be trusted to anticipate any need, solve any challenge and pursue any opportunity.

Ten reasons to choose NETCONNECT®

1. One copper/fibre portfolio for all your structured cabling enterprise LAN, data centre and campus applications
2. Optimised performance through ongoing third-party testing of copper solutions
3. WebTrak® tracks cables through the manufacturing process and provides online access to test reports to verify performance
4. NETCONNECT 25-year Solutions Warranty
5. Global support with NETCONNECT-certified installation companies, plus CommScope technical and field sales experts
6. Certified NETCONNECT installer training ensures structured cabling is always properly installed
7. Global R&D effort with more than 10,000 patents and patent applications
8. Superior, consistent cable terminations with the SL-installation tool
9. Multiple RJ45 jack options accommodate M-series, SL and keystone faceplates
10. Significant stock available from authorised NETCONNECT distributors

NETCONNECT COPPER SOLUTIONS

The NETCONNECT family of copper products includes twisted-pair cabling and patch cords, panels, jacks and accessories for your Category 6A and Category 6 channels.

From the data centre to in-building connectivity, NETCONNECT Category 6A solutions satisfy a growing list of network applications, including Wi-Fi, Power over Ethernet and 10GBASE-T. All NETCONNECT Category 6A solutions are available in U/UTP and F/UTP options and comply with the relevant ISO/IEC 11801 standards. Category 7A and Category 7 cable is also available.





Figure 1. Typical horizontal channel design

Category 6A


CS67 AND CS54 CABLE:

CommScope offers Category 7A S/FTP (CS67) and Category 7 S/FTP and F/FTP (CS54) cables; both of which can be deployed as part of a Category 6A compliant channel with the appropriate NETCONNECT jacks and patch-cords. These cables are available with LSZH sheaths in several CPR Euroclasses.



CS44 CABLE:

CommScope's CS44Z, CS44R and CS44P Category 6A cables are guaranteed to meet Category 6A specifications. Cables are available in different jacket types: LSZH, Riser and Plenum in unshielded twisted-pair (U/UTP) or foil-shielded twisted-pair constructions. They are also available in a number of CPR Euroclasses. Foil shield pair cable is available on reels, while U/UTP cable is also available in convenient, easy-to-store CommPak boxes.



PATCH PANELS:

Category 6A patch panels are available in unshielded and shielded options, as well as flat and angled designs. Unshielded panels are available either equipped with distribution modules or in the discrete distribution module design, which accepts jacks ordered separately. Shielded panels are available only in the discrete distribution module design, with jacks ordered separately.



NETCONNECT COPPER SOLUTIONS

Category 6A

JACKS:

The SLX shielded jack builds on the industry leading features of the existing AMP-TWIST shielded SL jacks. Support for a wide range of colour options and built-in support for dust covers. Termination is done via the existing SL termination tool with Direct Screen Termination support making screen termination simple and secure.




The SLX Cat 6A jack has been externally verified to meet Category 6A component compliance ISO/IEC 11801-1 Ed.1.0 (2017-11). The SL-style unshielded jack is also built on SL-technology and termination methods, and is available in a range of colours, with or without dust covers.



PATCH CORDS:

NETCONNECT Category 6A patch cords deliver superior electrical performance. Available in shielded and unshielded options, they utilise transparent, flexible slim-line boots providing for high density switch applications and accept the CommScope line of colour clips to assist in circuit identification and patch cord management.



NETCONNECT COPPER SOLUTIONS


Category 6

CS31 CABLE:

CommScope's CS31 Category 6 cables are guaranteed to meet Category 6 specifications. Cables are available in LSZH, Riser and CM jacket types.

CS34 CABLE:

CommScope's CS34Z, CS34R and CS34P Category 6 cables are guaranteed to meet Category 6 specifications. Cables are available in different jacket types: LSZH, Riser and Plenum, in unshielded twisted-pair (U/UTP) or foil-shielded twisted-pair constructions. They are available in a number of CPR Euroclasses. Shielded Category 6 cable is available on reels, while U/UTP cable is also available in convenient, easy-to-store CommPak boxes.



PATCH PANELS:

Category 6 patch panels are available in unshielded and shielded options, as well as flat and angled designs. Unshielded panels are available either equipped with distribution modules or in the discrete distribution module design, which accepts jacks ordered separately. Shielded panels are available only in the discrete distribution module design, with jacks ordered separately.



JACKS:

The SLX shielded jack builds on the industry leading features of the existing AMP-TWIST shielded SL jacks. Support for a wide range of colour options and built-in support for dust covers. Termination is done via the existing SL termination tool with Direct Screen Termination support making screen termination simple and secure.




The SLX Cat 6 jack has been externally verified to meet Category 6 component compliance ISO/IEC 11801-1 Ed.1.0 (2017-11). Unshielded jacks are available for SL and Keystone faceplates. Both are built on SL-technology and termination methods, and are available in a range of colours.



PATCH CORDS:

NETCONNECT Category 6 patch cords deliver superior electrical performance. Available in shielded and unshielded options, they utilise transparent, flexible slim-line boots providing for high density switch applications and accept the CommScope line of colour clips to assist in circuit identification and patch cord management.



NETCONNECT FIBRE SOLUTIONS

With multimode and singlemode options, NETCONNECT fibre solutions support applications ranging from campus and outside plant installations to data centres, buildings and fibre to the desktop. Modular connectivity components—including fibre enclosures and patch panels, pre-terminated cassettes, modules and adapters—enable you to deploy quickly and migrate easily as your needs grow.

DISTRIBUTION CABLE AND MPO FIBRE CABLE ASSEMBLIES

NETCONNECT fibre cabling includes multimode and singlemode ruggedised fanout and distribution cables. MPO Cabling is available in multimode and singlemode as patch, trunk or fanout cable assemblies. Multiple fibre types and constructions make it suitable for a broad range of environments: OSP direct buried, duct and aerial, indoor/outdoor and indoor-only. The NETCONNECT fibre portfolio also includes a variety of termination options, from traditional field termination to fusion splicing and tool-less termination with CommScope's Qwik II connector technology.



WALL-MOUNT FIBRE ENCLOSURES

The WBE-EMT is a wall-mount fibre enclosure that handles splicing and termination of in-building fibre cable or outside plant cable. The enclosure can be configured for multiple adapter applications and is designed to accommodate the termination of up to 96 LC connections. By adding the appropriate splice holders, the enclosures can also house up to 96 single fusion splices, 72 mechanical splices or 36 mass fusion splices.



STANDARD-DENSITY FIBRE PATCH PANELS

Standard-density (SD) fibre patch panels support multimode and single fibre cable and MPO assemblies. Use it for expanding telecommunication closets to risers, in small data centres, intelligent building connectivity, education and government structures, and more. Available in 1U, 2U and 4U configurations, it holds three splice cassettes or preterminated modules—or 36 duplex LC (72 fibres) or 24 MPO pass-through adapters (288 fibres)—in each 1U of rack space. Completely modular for easy deployment and upgrades, it's a future-ready platform for all your fibre needs.



NETCONNECT FIBRE SOLUTIONS


FIBRE MODULES

The corresponding modules for the standard-density fibre panel feature a 1000-style footprint and are available with one or two 12-fibre MPO connections on the back. 1000-style fibre modules also support preterminated MPO trunk cables for rapid deployment in the data centre. All fibre modules are factory tested and ready for installation.



FIBRE SPLICE CASSETTES

Fibre splicing cassettes feature pre-installed fibre pigtails and support fusion splicing within the cassette. Select from OM4 and singlemode OS2 fibre, as well as LC, LC/APC, SC and SC/APC connectors.



FIBRE ADAPTER PACKS


Fibre adapter packs are available to accept OM3, OM4 and singlemode fibre and support LC, keyed LC, LC/APC, SC and SC/APC connectors.



POWERED FIBRE CABLE SYSTEM (PFCS)

CommScope's Powered Fibre Cable System (PFCS) distributes power and fibre within the same cable, simplifying the addition of new small cells, Wi-Fi access points and IP cameras. In doing so, it can deliver low voltage power from a centralised source without the need of installing extra conduits, transformers or remote uninterrupted power supplies (UPS).

The Powered Fibre Cable System is comprised of hybrid cables and PoE Extenders, along with power transmission management, safety and overload protection as well as a universal power supply (PSU).



For more information on the Powered Fibre Cable System, please refer to the [PFCS solutions guide](#).



Complete confidence, end to end

The NETCONNECT solutions portfolio offers a full range of copper and fibre cable and connectivity, all designed for the superior mating and reliable performance your system needs. Working together across your entire network, NETCONNECT solutions provide a complete infrastructure platform—copper to fibre, outside to inside, backbone to the desktop.

And, with CommScope's Certified Installer Program, installation is handled by trained experts with demonstrated proficiency in areas such as industry codes and standards, infrastructure design, terminations, splicing, testing and troubleshooting. So you know it's done right.

Complete, compatible solutions from a single trusted source: That's NETCONNECT from CommScope.

Driven. Dynamic. Dedicated.

Our 40 years of proven experience testifies to our ability to anticipate any need, solve any challenge and pursue any opportunity. With a history of results and a focus on tomorrow, CommScope is the premier choice for smarter and faster performance. With each new improvement to your network infrastructure, we are readying you for the future. To learn more, contact your CommScope account executive or visit www.commscope.com.

Let's get started.

CommScope pushes the boundaries of communications technology with game-changing ideas and ground-breaking discoveries that spark profound human achievement. We collaborate with our customers and partners to design, create and build the world's most advanced networks. It is our passion and commitment to identify the next opportunity and realise a better tomorrow. Discover more at commscope.com

COMMSCOPE®

commscope.com

Visit our website or contact your local CommScope representative for more information.

© 2018 CommScope, Inc. All rights reserved.

Unless otherwise noted, all trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services. CommScope is committed to the highest standards of business integrity and environmental sustainability with a number of CommScope's facilities across the globe certified in accordance with international standards, including ISO 9001, TL 9000, and ISO 14001. Further information regarding CommScope's commitment can be found at www.commscope.com/About-Us/Corporate-Responsibility-and-Sustainability.

BR-112972.1-EN.GB (10/18)

25-year warranty

CommScope stands behind our NETCONNECT solutions with a 25-year warranty for both performance and reliability. We guarantee all NETCONNECT solutions products are free from material and workmanship defects, and that a properly designed, installed, tested and registered structured cabling system will support any application designed to communicate via media specified by ANSI/TIA 568-C series standards. This warranty applies to NETCONNECT solutions installed in structured cabling systems and that have been installed and maintained by a NETCONNECT certified installer.