


E#O® Coaxial/Microduct Hybrid Buried Cable



- E#O is a solution that enables service providers the ability to bridge HFC networks to FTTx. The E#O composite coaxial/fiber product line combines fiber, microducts, and coaxial cable preinstalled in conduit
- Serves businesses in a new commercial serving area
- Mitigates future cost of fiber installation
- Pre-installed in high density PE conduit for added physical protection
- One-step installation saves on construction cost
- Ideal for commercial data customers that also require video
- All products tested to industry standards
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Coaxial fiber cable-in-conduit
Product Brand	E#O®
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Cable Series	P3 875
---------------------	--------

Dimensions

Height	48.26 mm 1.9 in
Width	48.26 mm 1.9 in
Outer Jacket Thickness, nominal	3.835 mm 0.151 in

Material Specifications

Outer Jacket Material	High density polyethylene (HDPE)
------------------------------	----------------------------------

Mechanical Specifications

Minimum Bend Radius	508 mm 20 in
Pulling Tension, maximum	659.977 kg 1455 lb

Environmental Specifications

Environmental Space Buried

Packaging and Weights

Weight, gross 836.348 kg/km | 562 lb/kft

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

- 360000000 – ConQuest® Empty Conduit, 12.7 mm, black
- 5309193 P3® 875 JCASS – 75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground
- CX3799839 200T135 EMPTY DUCT COEX – ConQuest® Empty Conduit, 2 in, SDR 13.5, terracotta

360000000



ConQuest® Empty Conduit, 12.7 mm, black

Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Black
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Inner Diameter, nominal	10.008 mm 0.394 in
Outer Diameter, nominal	12.7 mm 0.5 in
Wall Thickness, minimum	1.346 mm 0.053 in
Nominal Size	12.7 mm

Material Specifications

Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min

360000000

Mechanical Specifications

Minimum Bend Radius, unsupported	152.4 mm 6 in
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	20.684 N/mm ² 3000 psi
Pulling Tension, maximum	86.183 kg 190 lb

Environmental Specifications

Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net	46.133 kg/km 31 lb/kft
--------------------	--------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance

75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground



Product Classification

Product Type	Coaxial hardline cable
Product Brand	P3®
Warranty	One year

General Specifications

Cable Type	875 Series
Construction Type	Swaged
Jacket Color	Black
Short Description	P3 875 JCASS SM PR997

Dimensions

Cable Length	762 m 2500 ft
Diameter Over Center Conductor, nominal	4.928 mm 0.194 in
Diameter Over Dielectric, nominal	20.244 mm 0.797 in
Diameter Over Jacket, nominal	24.257 mm 0.955 in
Diameter Over Outer Conductor, nominal	22.225 mm 0.875 in
Jacket Thickness, nominal	0.889 mm 0.035 in
Outer Conductor Thickness, nominal	0.991 mm 0.039 in

Electrical Specifications

Capacitance	50.197 pF/m 15.3 pF/ft
Capacitance Tolerance	±1.0 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±2 ohm

dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	1.378 ohms/km 0.42 ohms/kft
dc Resistance, Loop, nominal	1.804 ohms/km 0.55 ohms/kft
dc Resistance, Outer Conductor, nominal	0.427 ohms/km 0.13 ohms/kft
Jacket Spark Test Voltage	5000 Vac
Nominal Velocity of Propagation (NVP)	87 %
Operating Frequency Band	5–3000 MHz
Structural Return Loss	24 dB @ 1003–1218 MHz 24 dB @ 1219–1794 MHz 30 dB @ 5–1002 MHz
Structural Return Loss, Grade N	≥24 dB @ 1003–1218 MHz ≥24 dB @ 1219–1794 MHz ≥30 dB @ 5–1002 MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.3	0.09
55.0	1.08	0.33
85.0	1.31	0.4
204.0	2.07	0.63
211.0	2.17	0.66
250.0	2.36	0.72
300.0	2.56	0.78
350.0	2.76	0.84
400.0	2.99	0.91
450.0	3.18	0.97
500.0	3.38	1.03
550.0	3.54	1.08
600.0	3.74	1.14
750.0	4.23	1.29
865.0	4.63	1.41
1002.0	5.02	1.53
1218.0	5.57	1.7
1500.0	6.39	1.95
1794.0	7.13	2.17
1800.0	7.14	2.18
2000.0	7.62	2.32

5309193 | P3® 875 JCLASS

2200.0	8.09	2.46
2500.0	8.76	2.67
2700.0	9.19	2.8
3000.0	9.83	3

Material Specifications

Center Conductor Material	Copper-clad aluminum
Dielectric Material	Foam PE
Jacket Material	PE
Outer Conductor Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded	177.8 mm 7 in
Pulling Tension, maximum	396.893 kg 875 lb

Environmental Specifications

Corrosion Protection	Migraheal®
Environmental Space	Buried

Packaging and Weights

Packaging Type	Reel
Weight, gross	505.976 kg/km 340 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system





ConQuest® Empty Conduit, 2 in, SDR 13.5, terracotta

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Empty conduit
Product Brand	ConQuest®
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Color	Terracotta
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	762 m 2500 ft
Inner Diameter, nominal	50.876 mm 2.003 in
Outer Diameter, nominal	60.325 mm 2.375 in
Wall Thickness Designation	SDR 13.5
Wall Thickness, minimum	4.47 mm 0.176 in
Nominal Size	2 in

Material Specifications

Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790

CX3799839 | 200T135 EMPTY DUCT COEX

Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported	660.4 mm 26 in
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	20.684 N/mm ² 3000 psi
Pulling Tension, maximum	1,170.268 kg 2580 lb

Environmental Specifications

Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net	791.703 kg/km 532 lb/kft
--------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance