

NGFB-TB4MLU



Next Generation Frame (NGF) Fiber Termination Block with IFC cable, 144 SC/UPC to Stub tail, singlemode, right oriented, upward cable exit, black, 31 meters

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber patch block, with IFC cable
Product Series	NGFB

General Specifications

Functionality	Patching
Application	Used in NGF-style frames only
Body Style	Right orientation
Cable Exit Location	Upward
Color	Black
Color, front	Black
Door Type, front	Compression latch Hinged
Growth Configuration	Fully loaded
Interface, front	Unloaded
Interface, rear	Stub tail
Rack Type	NGF
Shelf Movement	Fixed
Total Ports, quantity	144

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

NGFB-TB4MLU

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 80%, non-condensing

Qualification Standards Telcordia GR-449-CORE

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

