PM-SU4-63



Universal Sliding Pipe Mount Kit for 4-1/2 in OD x 63 in pipe

Product Classification

Product Type Pipe mount

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2

mm (8 in) OD

Note One 96 in x 8 in panel antenna per sector

Pipe, quantity 1

Tower Taper Tapered

Dimensions

 Height
 1,600.2 mm | 63 in

 Width
 304.8 mm | 12 in

 Length
 304.8 mm | 12 in

 Pipe Length
 1,600.2 mm | 63 in


 Mounting Diameter, maximum
 203.2 mm | 8 in

 Mounting Diameter, minimum
 0 mm | 0 in

Pipe Outer Diameter 114.3 mm | 4.5 in

PM-SU4-63

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Pipe | Sliding pipe mount brackets | Universal saddle mount

Packaging quantity 1

PM-SU4-63

Weight, net 62.6 kg | 138.009 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

MT-653-63 – Plain End Pipe, 4-1/2 in OD x 63 in x .237" A500C 46Ksi

PM-SL4 – Universal Taper Pipe Mount Slider Bracket for 4-1/2 in OD pipe

SM-U2080 – Universal Saddle Mount for straight or tapered legs up to 8 in OD, 8 in angle 60°, or 6 in angle

90° (Kit of 2)

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code



MT-653-63



Plain End Pipe, 4-1/2 in OD x 63 in x .237" A500C 46Ksi

Product Classification

Product Type Plain end pipe

General Specifications

Pipe, quantity 1

Dimensions

 Height
 114.3 mm | 4.5 in

 Width
 114.3 mm | 4.5 in

 Length
 1,600.2 mm | 63 in

 Pipe Length
 1,600.2 mm | 63 in

 Pipe Outer Diameter
 114.3 mm | 4.5 in

 Material Thickness
 6.02 mm | 0.237 in

Material Specifications

Material Type A500 | Hot dip galvanized steel

Material Grade C

Material Strength 46 KSI

Packaging and Weights

Included Pipe **Packaging quantity** 1

Weight, net 25.9 kg | 57.1 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

PM-SL4



Universal Taper Pipe Mount Slider Bracket for 4-1/2 in OD pipe

Product Classification

Product Type Pipe mount

General Specifications

Mounting Saddle mounts

Note One 96 in x 8 in panel antenna per pipe mount

Pipe, quantity 0

Tower Taper Tapered

Dimensions

 Height
 127 mm | 5 in


 Width
 152.4 mm | 6 in

 Length
 304.8 mm | 12 in

 Pipe Outer Diameter
 114.3 mm | 4.5 in

PM-SL4

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Hardware | Sliding pipe mount brackets

Packaging quantity 2

PM-SL4

Weight, net 14.2 kg | 31.306 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code



SM-U2080



Universal Saddle Mount for straight or tapered legs up to 8 in OD, 8 in angle 60°, or 6 in angle 90° (Kit of 2)

Product Classification

Product Type Saddle mount

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2

mm (8 in) OD

Tower Taper Non-tapered

Dimensions

 Height
 152.4 mm | 6 in

 Width
 279.4 mm | 11 in

 Length
 254 mm | 10 in

 Mounting Diameter, maximum
 203.2 mm | 8 in

 Mounting Diameter, minimum
 0 mm | 0 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Mount
Packaging quantity 2

Weight, net 22.7 kg | 50.045 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

SM-U2080

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

