5NPX1006F-V2



10-port multibeam antenna, 10x 1710–2180 MHz, 5x 10-14° HPBW, fixed electrical tilt

General Specifications

Antenna Type Multibeam

Band Single band

Color Light Gray (RAL 7035)

Grounding Type RF connector inner conductor and body grounded to reflector and mounting bracket

Performance Note Outdoor usage

Radome Material ASA, UV stabilized

Radiator Material Brass | Low loss circuit board

Reflector Material Aluminum

RF Connector Interface 4.3-10 Female

RF Connector Location Bottom
RF Connector Quantity, high band 10

RF Connector Quantity, total 10

Dimensions

 Width
 864 mm | 34.016 in

 Depth
 202 mm | 7.953 in

 Length
 889 mm | 35 in

 Net Weight, without mounting kit
 30 kg | 66.139 lb

Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1710 – 2180 MHz

Polarization ±45°

Electrical Specifications

Frequency Band, MHz 1710-1920 1920-2180

COMMSCOPE®

5NPX1006F-V2

Gain, dBi	21.7	22.3
Beamwidth, Horizontal, degrees	13	12
Beamwidth, Vertical, degrees	11.9	10.9
Beam Tilt, degrees	6	6
USLS (First Lobe), dB	14	16
Front-to-Back Ratio at 180°, dB	32	34
Isolation, Same Beam, dB	25	25
VSWR Return loss, dB	1.43 15.0	1.43 15.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150
Input Power per Port, maximum, watts	300	300

Electrical Specifications, BASTA

Frequency Band, MHz	1710-1920	1920-2180
Gain by all Beam Tilts, average, dBi	20.7	21.3
Gain by all Beam Tilts Tolerance, dB	±2	±1.7
Beamwidth, Horizontal Tolerance, degrees	±2.1	±1.7
Beamwidth, Vertical Tolerance, degrees	±0.7	±0.7
USLS, beampeak to 20° above beampeak, dB	17	18
Front-to-Back Total Power at 180° ± 30°, dB	30	32
CPR at Boresight, dB	9	10

Mechanical Specifications

Wind Loading @ Velocity, frontal	931.0 N @ 150 km/h (209.3 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	113.0 N @ 150 km/h (25.4 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	931.0 N @ 150 km/h (209.3 lbf @ 150 km/h)
Wind Coard marriagemen	050 kmg /b (155 mg mb)

Wind Speed, maximum 250 km/h (155 mph)

Packaging and Weights

Width, packed	977 mm 38.465 in
Depth, packed	349 mm 13.74 in
Length, packed	1038 mm 40.866 in
Weight, gross	47 kg 103.617 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

5NPX1006F-V2

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

T-045-GL-E – Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

