


A-100534

Base Product



Outdoor Transmission Cabinet

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type	Micro cell site enclosure
Ordering Note	For UK region only

General Specifications

Access	Front door
Batteries Supported	4
Cabinet Type	Integrated cabinet
Color	Gray Green (RAL 6009) Light Gray (RAL 7035) Others available at additional cost
Cooling	175 mm fan (1)
Door Security	Swing handle with European profile cylinder
Doors, quantity	1
Mounting	Plinth Root
Rack Type	EIA 19 in
Rack Units	18

Dimensions

Height	1,422.4 mm 56 in
Width	609.6 mm 24 in
Depth	609.6 mm 24 in

Electrical Specifications

Input Power Supply	1U PSU 1.6KW Max
ac Distribution Type	8-way plastic enclosure

A-100534

Battery String Current, maximum	33 A-h @ 48 Vdc
dc Distribution Type	8-way dc panel Power supply unit
Generator Connection	No connection
Power Phase	Single
Rectifier Power	800 W
Rectifiers, quantity	2
Voltage	230 Vac

Material Specifications

Finish	Powder coated
Material Type	Galvanized steel

Environmental Specifications

Qualification Standards	IEC 60529: 2001 IEE Wiring Regulations BS 7671 IP55
--------------------------------	---

Packaging and Weights

Included	-48V DC Power supply unit Batteries Brackets Cooling Installation Kit Power Distribution
Weight, net	110.223 kg 243 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system