

UGGRXUCZR



Hybrid Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 (Pinned) to Unconnectorized , 4 Pair 16AWG Constellation Trunk Cable Assembly, 16-Fiber, Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Hybrid cable assembly 4-pair
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications

Conductor Capacitance	75.459 pF/m 23 pF/ft
Conductor Resistance	14.698 ohms/km 4.48 ohms/kft
Conductor Type	16 AWG Stranded
Conductors, quantity	8
Conductor Pairs, quantity	4
Connector A, quantity	1
Color, boot A	Black
Color, connector A	Green
Construction Type	Hybrid standard trunk
Furcation Color	Yellow
Interface, Connector A	MPO-16/APC Male
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	16
Total Fibers, quantity	16

Dimensions


Breakout Length	24 in 72 in
------------------------	---------------

UGGRXUCZR


Cable Assembly Length Range (m) 10 – 999

Cable Assembly Length Range (ft) 33 – 999

Dimension Drawing



Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

UGGRXUCZR

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Indoor Plenum
Qualification Standards	GR-3108 class 4

Included Products

860661398	–	Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, pinned, green, for 3 mm cable
-----------	---	--