

MR3919-000 | FDSC-GATOR-12F-T



Gator 12F Fiber Optic Splice Closure, Re-enterable, Gel Cable sealing, for up to 12 splices

- Designed for splicing two loose tube “flat drop” style cables of 1 to 12 fibers in above grade, below grade, and direct buried applications
- Uses gel sealing technology to create a sealed closure system that will fit into confined areas such as small “flowerpot” style handholes
- Incorporates our unique cable hold down and strength member termination features and is capable of holding either fusion or mechanical splices
- Tone wires can also be terminated outside of the closure using the included hardware

Alternative products available:

MR3919-000-US	Gator 12F Fiber Optic Splice Closure, Re-enterable, Gel Cable sealing, for up to 12 splices, Build America Buy America (BABA)
FDSC-GATOR-12F-T	

Product Classification

Regional Availability	Latin America North America
Product Type	Single-ended, flat fiber closure
Product Series	FDSC GATOR

General Specifications

Cable Entry Drop Port Style	Flat
Cable Entry Main Port Style	Flat
Cable Ports Quantity, total	2 round ports
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Wall
Network Area Type	Drop
Splicing Capacity, Mass Fusion, maximum	12
Splicing Capacity, Single Fusion, maximum	12
Splicing Type, Supported	Mass fusion Single fusion

MR3919-000 | FDSC-GATOR-12F-T

Dimensions

Height	30.48 mm 1.2 in
Width	147.32 mm 5.8 in
Length	190.5 mm 7.5 in

Environmental Specifications

Environmental Space	Below ground Buried
----------------------------	-----------------------

Packaging and Weights

Packaging quantity	10
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

