

APTDC-BDFDM-DB



Arrestor Plus® LTE Band Quarterwave dc Passing Surge Arrestor (T-shaped), 698–2700 MHz, with interface types DIN Female Bulkhead and DIN Male

Product Classification

| | |
|----------------------|---|
| Product Type | Surge arrester |
| Product Brand | Arrestor Plus® |
| Ordering Note | CommScope® standard product in Asia Pacific |

General Specifications


| | |
|------------------------------|--------------------------|
| Device Type | dc Pass |
| Body Style | Bulkhead |
| Inner Contact Plating | Silver |
| Interface | 7-16 DIN Female Bulkhead |
| Interface 2 | 7-16 DIN Male |
| Outer Contact Plating | Trimetal |
| Pressurizable | No |

Dimensions

| | |
|---------------|------------------|
| Height | 88 mm 3.465 in |
| Width | 42 mm 1.654 in |
| Length | 88 mm 3.465 in |

Outline Drawing

APTDC-BDFDM-DB



Electrical Specifications

| | |
|---|----------------------|
| 3rd Order IMD | -117 dBm |
| 3rd Order IMD Test Method | Two +43 dBm carriers |
| Insertion Loss, typical | 0.07 dB |
| Average Power | 3000 W |
| Connector Impedance | 50 ohm |
| dc Current, continuous | 3 A |
| Gas Tube Voltage | 350 V |
| Lightning Surge Capability | 10 times @ 30 kA |
| Lightning Surge Capability Test Method | IEEE C62.42-1991 |
| Lightning Surge Capability Waveform | 8/20 waveform |
| Lightning Surge Current | 30 kA |
| Lightning Surge Current Waveform | 8/20 waveform |
| Operating Frequency Band | 698 – 2700 MHz |
| Peak Power, maximum | 40 kW |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 2.0–2.3 MHz | 1.135 | 24 |

APTDC-BDFDM-DB

| | | |
|----------------------|-------|------|
| 698–806 MHz | 1.253 | 19 |
| 806–960 MHz | 1.135 | 24 |
| 1710–2200 MHz | 1.135 | 24 |
| 2200–2700 MHz | 1.208 | 20.5 |

Mechanical Specifications

| | |
|--|---|
| Attachment Durability | 25 cycles |
| Coupling Nut Proof Torque | 220 in lb 24.857 N-m |
| Coupling Nut Retention Force | 1,000.85 N 225 lbf |
| Coupling Nut Retention Force Method | MIL-C-39012C-3.25, 4.6.22 |
| Interface Durability | 500 cycles |
| Interface Durability Method | IEC 61169-16:9.5 |
| Mechanical Shock Test Method | MIL-STD-202F, Method 213B, Test Condition C |

Environmental Specifications

| | |
|---|---|
| Operating Temperature | -40 °C to +100 °C (-40 °F to +212 °F) |
| Storage Temperature | -70 °C to +150 °C (-94 °F to +302 °F) |
| Attenuation, Ambient Temperature | 20 °C 68 °F |
| Average Power, Ambient Temperature | 40 °C 104 °F |
| Corrosion Test Method | MIL-STD-202, Method 101, Test Condition B |
| Immersion Depth | 1 m |
| Immersion Test Mating | Mated |
| Immersion Test Method | IEC 60529:2001, IP68 |
| Moisture Resistance Test Method | MIL-STD-202, Method 106 |
| Thermal Shock Test Method | MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C |
| Water Jetting Test Mating | Mated |

Packaging and Weights

| | |
|--------------------|--------------------|
| Weight, net | 0.599 kg 1.32 lb |
|--------------------|--------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

APTDC-BDFDM-DB

| | |
|------------|--|
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant |



* Footnotes

| | |
|--------------------------------|---|
| Insertion Loss, typical | 0.05√freq (GHz) (not applicable for elliptical waveguide) |
| Immersion Depth | Immersion at specified depth for 24 hours |