760152561 | 360-IPR-1100-E-GS3-1U-24



SYSTIMAX 360™ GigaSPEED XL® 1100GS3 Evolve Category 6 U/UTP Patch Panel, 24 port

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio SYSTIMAX®

 Product Type
 RJ45 patch panel

 Product Brand
 GigaSPEED XL®

Product Series UTG

General Specifications

ANSI/TIA Category 6

Cable Type Unshielded

Color Cool gray | Satin chrome

Conductor Type Solid | Stranded

Intelligence Type iPatch® ready

Modules, quantity 4

Panel StyleStraightRack TypeEIA 19 in

Rack Units 1

Termination Type IDC

Total Ports, quantity 24

Transmission StandardsANSI/TIA-568.2-D | ISO/IEC 11801 Class E

Wiring T568A | T568B

Dimensions

Height44.45 mm| 1.75 inWidth482.6 mm| 19 inDepth, with cable management165.1 mm| 6.5 inCompatible Diameter Over Dielectric, maximum1.168 mm| 0.046 in

Page 1 of 3



760152561 | 360-IPR-1100-E-GS3-1U-24

Compatible Diameter Over Dielectric, minimum0.762 mm0.03 inCompatible Conductor Gauge, solid22 AWG24 AWGCompatible Conductor Gauge, stranded22 AWG24 AWG

Electrical Specifications

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

Remote PoweringFully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable

when installed according to ISO/IEC 14763-2, CENELEC EN

50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Material Specifications

Contact Plating Material Precious metals

Material Type High-impact, flame retardant, thermoplastic | Powder-

coated steel

Termination Contact Plating Nickel

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Insertion Life, test plug IEC 60603-7 compliant plug

Plug Retention Force, minimum 133 N | 29.9 lbf

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative HumidityUp to 95%, non-condensing

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

Packaging and Weights

Packaging Material Eco-friendly, single-use plastics-free

Packaging quantity 1



760152561 | 360-IPR-1100-E-GS3-1U-24

Weight, net 0.862 kg | 1.9 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

