Heat treated LDF1RK-50, HELIAX® Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated fire retardant jacket

Product Classification

Product Type Coaxial wireless cable

Product Brand HELIAX®
Product Series LDF1-50

General Specifications

Flexibility Standard

Jacket Color Black

Performance NoteAttenuation values typical, guaranteed within 5%

Dimensions

 Diameter Over Dielectric
 6.858 mm | 0.27 in

 Diameter Over Jacket
 9.017 mm | 0.355 in

 Inner Conductor OD
 2.54 mm | 0.1 in

 Outer Conductor OD
 7.874 mm | 0.31 in

Nominal Size 1/4 in

Electrical Specifications

Cable Impedance 50 ohm ±1 ohm

Capacitance 77 pF/m | 23.47 pF/ft

dc Resistance, Inner Conductor5.151 ohms/km | 1.57 ohms/kftdc Resistance, Outer Conductor4.003 ohms/km | 1.22 ohms/kft

dc Test Voltage 2200 V

Inductance $0.059 \, \mu H/m \, \mid \, 0.018 \, \mu H/ft$

Insulation Resistance 100000 MOhms-km

Jacket Spark Test Voltage (rms) 5000 V

Operating Frequency Band 1 – 15800 MHz

 Peak Power
 12.1 kW

 Velocity
 86 %



VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680-960 MHz	1.201	20.79
1700-2200 MHz	1.201	20.79
2200-2700 MHz	1.433	14.99

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.394	0.12	12.1
1.5	0.483	0.147	12.1
2.0	0.558	0.17	12.1
10.0	1.254	0.382	5.83
20.0	1.781	0.543	4.11
30.0	2.188	0.667	3.34
50.0	2.838	0.865	2.58
85.0	3.724	1.135	1.96
88.0	3.791	1.156	1.93
100.0	4.049	1.234	1.81
108.0	4.213	1.284	1.74
150.0	4.993	1.522	1.47
174.0	5.392	1.644	1.36
200.0	5.798	1.767	1.26
204.0	5.858	1.785	1.25
300.0	7.168	2.185	1.02
400.0	8.342	2.543	0.88
450.0	8.88	2.706	0.82
460.0	8.984	2.738	0.81
500.0	9.391	2.862	0.78
512.0	9.511	2.899	0.77
600.0	10.351	3.155	0.71
700.0	11.244	3.427	0.65
800.0	12.084	3.683	0.61
824.0	12.278	3.742	0.6
894.0	12.833	3.911	0.57

Page 2 of 5

35422-57

960.0	13.339	4.066	0.55
1000.0	13.639	4.157	0.54
1218.0	15.192	4.63	0.48
1250.0	15.41	4.697	0.47
1500.0	17.04	5.194	0.43
1700.0	18.266	5.567	0.4
1794.0	18.823	5.737	0.39
1800.0	18.858	5.748	0.39
2000.0	20.003	6.097	0.37
2100.0	20.559	6.266	0.36
2200.0	21.104	6.432	0.35
2300.0	21.64	6.596	0.34
2500.0	22.686	6.914	0.32
2700.0	23.701	7.224	0.31
3000.0	25.171	7.672	0.29
3400.0	27.048	8.244	0.27
3600.0	27.956	8.521	0.26
3700.0	28.403	8.657	0.26
3800.0	28.846	8.792	0.25
3900.0	29.284	8.925	0.25
4000.0	29.719	9.058	0.25
4100.0	30.149	9.189	0.24
4200.0	30.576	9.319	0.24
4300.0	30.999	9.448	0.24
4400.0	31.419	9.576	0.23
4500.0	31.835	9.703	0.23
4600.0	32.249	9.829	0.23
4700.0	32.659	9.954	0.22
4800.0	33.066	10.078	0.22
4900.0	33.47	10.201	0.22
5000.0	33.871	10.323	0.22
6000.0	37.742	11.503	0.19
8000.0	44.888	13.681	0.16
8800.0	47.579	14.501	0.15
10000.0	51.475	15.689	0.14

Page 3 of 5

35422-57

12000.0	57.664	17.575	0.13
14000.0	63.552	19.37	0.12
15800.0	68.646	20.922	0.11

Material Specifications

Dielectric Material Foam PE

Jacket Material Non-halogenated, fire retardant polyolefin

Inner Conductor Material Copper-clad aluminum wire

Outer Conductor Material Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends76.2 mm | 3 inMinimum Bend Radius, single Bend38.1 mm | 1.5 in

Number of Bends, minimum 15
Number of Bends, typical 30

 Tensile Strength
 91 kg | 200.62 lb

 Bending Moment
 1.4 N-m | 12.391 in lb

 Flat Plate Crush Strength
 1.4 kg/mm | 78.396 lb/in

Environmental Specifications

Installation temperature $-40 \, ^{\circ}\text{C to } +60 \, ^{\circ}\text{C (-40 \, ^{\circ}\text{F to } +140 \, ^{\circ}\text{F})}$ Operating Temperature $-40 \, ^{\circ}\text{C to } +60 \, ^{\circ}\text{C (-40 \, ^{\circ}\text{F to } +140 \, ^{\circ}\text{F})}$ Storage Temperature $-40 \, ^{\circ}\text{C to } +60 \, ^{\circ}\text{C (-40 \, ^{\circ}\text{F to } +140 \, ^{\circ}\text{F})}$

Attenuation, Ambient Temperature68 °F | 20 °CAverage Power, Ambient Temperature104 °F | 40 °CAverage Power, Inner Conductor Temperature212 °F | 100 °C

Fire Retardancy Test Method NFPA 130-2010 | UL 1666/CATVR

Smoke Index Test Method IEC 61034

Toxicity Index Test Method IEC 60754-1 | IEC 60754-2

Packaging and Weights

Cable weight 0.09 kg/m | 0.06 lb/ft

Regulatory Compliance/Certifications

COMMSCOPE®

35422-57

Agency

Classification

ISO 9001:2015



Designed, manufactured and/or distributed under this quality management system

