



FOSC® 600 D Fiber Optic Splice Closure, Gel Cable sealing, inline type, no pre-installed trays, loose buffered. Ribbon module, two 4-port gel blocks, storage basket, 4 ground feedthru lugs, with test valve

- Single-ended or in-line, gel-sealed closure for splicing feeder and distribution cables
- Excellent consolidation or rehabilitation closure with large fiber splicing capacity
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability	Latin America North America
Product Type	In-line, rectangular fiber closure Single-ended, rectangular fiber closure
Product Brand	FOSC®
Product Series	FOSC 600

General Specifications

Cable Entry Drop Port Style	Gel block
Cable Entry Main Port Style	Gel block
Cable Ports Quantity, total	4 multi-out ports (16 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Captured bolts Over-centered latches with rubber gasket
Closure Style	In-line Single-ended
Color	Black
Fiber Storage Basket Type	LBT standard size
Flash Test Valve	Pre-installed
Ground Feed-through	Included
Mounting	Pole Strand Wall
Network Area Type	Feeder Trunk
Splice Tray Included, quantity	0
Splice Tray Type Included	No trays
Splicing Capacity, Mass Fusion, maximum	1728

522352-000 | FOSC600-D8I-NT-0-M4V

Splicing Capacity, Single Fusion, maximum	864
Splicing Capacity, Single Splice, 12 fibers, maximum	864
Splicing Capacity, Single Splice, 6 fibers, maximum	324
Splicing Type, Supported	Mass fusion Single fusion

Dimensions

Height	254 mm 10 in
Width	274 mm 10.787 in
Length	828 mm 32.598 in
Main Cable Diameter, maximum	35 mm 1.378 in

Ordering Tree

FOSC 600 - X X X - XX - X - X X X

Closure Size

C	600 C
D	600 D

Number of Drop Cable Parts

4	One 4-port gel block
6	Two 3-port gel blocks
8	Two 4-port gel blocks

Configuration

B	Butt
I	In-Line
R	Reverse Butt*

Capacity (or type) of Splice Trays

36	D tray with six SM6 modules*
72	D tray with six SM12 modules 96
R2	D ribbon tray (splice capacity: 24, 12 fiber ribbon splices)
NT	No trays

Valve for Flash Test

V	V for valve is standard
---	-------------------------

Number of Ground Feed-Through Lugs

0	0 lugs
2	2 lugs
4	4 lugs

Slack Basket Type

C	Standard
D	Basket for D version
N	No basket
L	Loose buffer tube ribbon modification (D size only). No basket included.
M	Same as "L" above, but includes storage basket.

Number of Splice Trays

0 or 1	0 or 1 is standard
--------	--------------------

*For use when increased fiber lengths on tray is required and loose buffer tube cable reverse point is offset in main cable opening.

Material Specifications

Material Type	Rugged polymer
----------------------	----------------

Environmental Specifications

Environmental Space	Below ground Buried
----------------------------	-----------------------

522352-000 | FOSC600-D8I-NT-0-M4V

Qualification Standards

Telcordia GR-771-CORE, 20 ft waterhead

Water Resistance

Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity

1

Packaging Type

Box | Carton

Weight, net

11.79 kg | 25.992 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

