

760236119 | DM12iP-24LC-WB-ULL



G2 ULL Multimode OM5 MPO-12 Distribution Module, 2x12F MPO unpinned to 24F LC Lime Green, Method B Enhanced, iPatch Ready

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTIMAX ULL

General Specifications

Functionality	Breakout
Adapters, quantity, front	12
Adapters, quantity, rear	2
Color, front	Lime green
Color, rear	Lime green
Data Module Type	G2
Intelligence Type	iPatch® ready
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up MPO Non-Pinned
Polarity	Method B Enhanced (ULL)
Shuttered	No
Total Fibers, quantity	24
Total Ports, quantity, front	24

Dimensions

Height	24.64 mm 0.97 in
Width	94 mm 3.701 in

760236119 | DM12iP-24LC-WB-ULL

Depth 113.28 mm | 4.46 in

Optical Specifications

Fiber Mode Multimode
Fiber Type OM5, LazrSPEED® wideband
Insertion Loss Change, temperature 0.3 dB
Insertion Loss, maximum 0.35 dB

Environmental Specifications

Qualification Standards TIA/EIA-568-C.3
Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)