



DLX® Mini-MST, Fiber Optic Multiport Service Terminal, 4-port, round cable, 50 m/165 ft

- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- Multiport Service Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment

Product Classification

|                       |                                       |
|-----------------------|---------------------------------------|
| Regional Availability | EMEA                                  |
| Product Type          | Access terminal, without splitter/tap |
| Product Brand         | DLX®                                  |
| Product Series        | Mini-MST                              |

General Specifications


|                    |                              |
|--------------------|------------------------------|
| Cable Type         | Armored - Round - Loose Tube |
| Cable, quantity    | 1                            |
| Distribution Type  | 4 ports                      |
| Enclosure Color    | Gray                         |
| Mounting           | Handhole   Wall              |
| Port Type          | Hardened mini-size DLX       |
| Port, quantity     | 4                            |
| Splitter, quantity | 0                            |
| Stub Type          | Stub tail                    |

Dimensions


|                      |                     |
|----------------------|---------------------|
| Height               | 214.8 mm   8.457 in |
| Width                | 150 mm   5.906 in   |
| Depth                | 58.7 mm   2.311 in  |
| Cable Length, stub   | 165 ft (50 m)       |
| Cable Outer Diameter | 5.0 mm (0.20 in)    |

760235371 | MST-04FX00-U0050UM-IE-5MM

Dimension Drawing



Ordering Tree



Material Specifications

Enclosure Material Type

Gasketed hardened plastic

Optical Specifications

Fiber Type

G.657.A1/A2

Operating Wavelength Range

1260 – 1635 nm

Attenuation Terminal Connectors, maximum

0.4 dB

Insertion Loss, Terminal Connector, typical

0.16 dB

Return Loss, Connector, minimum

65 dB

Environmental Specifications

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity

5%–100%, condensing

Environmental Space

Above ground | Below ground

Qualification Standards

IEC 60529, IP65

UV Resistance

UV stabilized

Packaging and Weights

Packaging quantity

1

Packaging Type

Box | Carton

Weight, without cable

0.99 kg | 2.183 lb

Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

