





| ITEM | PART NO. | DESCRIPTION | QTY. | WEIGHT |
|------|----------------|-------------------------|------|------------|
| 1 | MTC79021414.01 | 14' SIDE CHANNEL | 2 | 159.09 LBS |
| 2 | MTC79021414.02 | GRATING SECTION BRACKET | 1 | 71.04 LBS |
| 3 | MTC79021416.02 | 14' CENTER CHANNEL | 5 | 154.79 LBS |
| 4 | MTC79020407.03 | 24" X 84" BAR GRATING | 14 | 99.90 LBS |
| 5 | MTC7902.03 | CHANNEL ADAPTER ANGLE | 10 | 7.07 LBS |
| 6 | GB-05205 | 5/8" X 2" GALV BOLT KIT | 42 | 0.12 LBS |
| 7 | GWF-05 | 5/8" GALV FLAT WASHER | 84 | 0.04 LBS |
| 8 | GCM03 | GRATING CLIP | 56 | 0.40 LBS |

| REVISIONS | | | | |
|-----------|------|-----------------|-----|----------|
| REV. | ZONE | DESCRIPTION | BY | DATE |
| A | | INITIAL RELEASE | OGG | 08/11/10 |

DETAIL A
SCALE 1 : 8



- NOTES:
- ALL METRIC DIMENSIONS ARE IN BRACKETS.
 - STAMP PART IDENTIFICATION NUMBER.
 - GRATING REMOVED FOR CLARITY.

| | | | |
|---|-------------------|--|---|
| These drawings and specifications are the proprietary property of ANDREW CORPORATION and may be used only for the specific purpose authorized in writing by Andrew Corporation. ALL DIMENSIONS ARE IN INCHES U.O.S. TOLERANCES UNLESS OTHERWISE SPECIFIED: .X = ± .12 ANGLES ±2° .XX = ± .06 FRACTIONS ±1/32 .XXX= ± .03 REMOVE BURRS AND BREAK EDGES .005 DO NOT SCALE THIS PRINT | DRAWN BY: OGG | SHEET: 1 of 1 | PART NUMBER: EQ-PI414-B |
| | CHECKED BY: TP | SCALE: NTS | DESCRIPTION: 14' X 14' PLATFORM |
| | DATE: 08/11/10 | MATERIAL: A36, A572 | DRAWING TYPE: ASSEMBLY DRAWING |
| | REVISION: A | FINISH: GALV A123 WEIGHT: 2672.66 LBS |  WESTCHESTER, IL. 60154 U.S.A. |