

10-port sector/multibeam antenna, 2x 694-960 and 8x 1695–2690 MHz, 65°|4x 33° HPBW, 5x RET

- Enhances network capacity and spectrum utilization when used in six sector applications
- Reduces antenna count to minimize Cap-Ex and Op-Ex costs 3 antennas required for 6 sector configurations
- Utilizes RET-PMOD-A20-5A12
- Conforms to RoHS 2011/65/EU

General Specifications

Antenna Type	Multibeam
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Radiator Material	Low loss circuit board
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, high band	8
RF Connector Quantity, low band	2
RF Connector Quantity, total	10

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Input Voltage	10-30 Vdc
Internal RET	High band (4) Low band (1)
Power Consumption, active state, maximum	10 W
Power Consumption, idle state, maximum	2 W
Power Consumption, normal conditions, maximum	10 W

Page 1 of 6



Protocol

3GPP/AISG 2.0 (Single RET)

1 1	m	זכו	\cap	הכ
1 1		ารเ	UЛ	17
-		 		. –

Width	395 mm 15.551 in
Depth	228 mm 8.976 in
Length	2499 mm 98.386 in
Net Weight, without mounting kit	39.2 kg 86.421 lb


Array Layout

			Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
			R1	694-960	1-2	1	CPxxxxxxxxxxxxxR1
¥2		Y4	Y1	1695-2690	3-4	2	CPxxxxxxxxxxxxXY1
			Y2	1695-2690	5-6	3	CPxxxxxxxxxxxXXXXXXY2
	R1		Y3	1695-2690	7-8	4	CPxxxxxxxxxxxXXXXXXXXXXY3
Y1		Y3	¥4	1695-2690	9-10	5	CPxxxxxxxxxxxxXY4

Bottom

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Page 2 of 6



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 694 – 960 MHz
Polarization	±45°
Total Input Power, maximum	1,200 W @ 50 °C

Electrical Specifications

Frequency Band, MHz	694-790	790-890	880-960	1695-188	0 1850–199	0 1920–218	0 2300–240	0 2490-2690
Gain, dBi	16.3	16.4	16.2	18.1	18.6	19.3	19.3	18.6
Beam Centers, Horizontal, degrees				±27	±27	±27	±27	±27
Beamwidth, Horizontal, degrees	65	66	67	39	39	37	33	34
Beamwidth, Vertical, degrees	9	8	7.2	7.9	7.4	7	6.2	5.8
Beam Tilt, degrees	2-12	2-12	2-12	2-12	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	17	19	15	16	16	17	18	19
Front-to-Back Ratio at 180°, dB	24	24	26	30	31	31	34	31
Front-to-Back Ratio, Copolarization 180° ± 30°, dB	24	24	25	23	25	27	30	28
Isolation, Cross Polarization, dB	25	25	25	28	28	28	28	28
Isolation, Inter-band, dB	30	30	30	28	28	28	28	28
Isolation, Beam to Beam, dB				28	28	28	28	28
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	300	300	300	200	200	200	200	200

Electrical Specifications, BASTA

Frequency Band, MHz	694-790	790-890	880-960	1695-1880) 1850–1990) 1920-2180	0 2300-2400) 2490-2690
Gain by all Beam Tilts, average, dBi	16.2	16.3	16	17.7	18.3	18.8	19	18.1
Gain by all Beam Tilts Tolerance, dB	±0.2	±0.3	±0.3	±0.7	±0.5	±0.6	±0.4	±0.6
Gain by Beam Tilt, average, dBi	2 ° 15.7 7 ° 15.9 12 ° 15.8	2 ° 16.0 7 ° 16.2 12 ° 16.1	2 ° 15.6 7 ° 15.8 12 ° 15.6	2 ° 17.1 7 ° 17.1 12 ° 16.9	2 ° 17.8 7 ° 17.8 12 ° 17.5	2 ° 18.2 7 ° 18.2 12 ° 17.8	2 ° 18.0 7 ° 17.9 12 ° 17.4	2 ° 17.4 7 ° 17.3 12 ° 17.0

Page 3 of 6



Beamwidth, Horizontal Tolerance, degrees	±1.4	±1.3	±1.9	±3.5	±2.6	±3.7	±2	±2.2
Beamwidth, Vertical Tolerance, degrees	±0.7	±0.4	±0.6	±0.5	±0.3	±0.4	±0.2	±0.2
USLS, beampeak to 20° above beampeak, dB	16	15	14	16	16	17	17	18
Front-to-Back Total Power at 180° ± 30°, dB	21	22	23	22	25	26	25	22
CPR at Boresight, dB	20	17	17	17	19	20	21	22
CPR at Sector, dB	7	8	14					
CPR at 10 dB Horizontal Beamwidth, dB				8	12	13	13	10

Mechanical Specifications

Wind Loading @ Velocity, frontal	525.0 N @ 150 km/h (118.0 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	386.0 N @ 150 km/h (86.8 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	898.0 N @ 150 km/h (201.9 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	540.0 N @ 150 km/h (121.4 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	505 mm 19.882 in
Depth, packed	386 mm 15.197 in
Length, packed	2631 mm 103.583 in
Weight, gross	53.2 kg 117.286 lb
Weight, net	39.2 kg 86.421 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

Page 4 of 6



BSAMNT-4

Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

Page 5 of 6



BSAMNT-4



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification	
Product Type	Downtilt mounting kit
General Specifications	
Application	Outdoor
Color	Silver
Dimensions	
Compatible Diameter, maximum	115 mm 4.528 in
Compatible Diameter, minimum	60 mm 2.362 in
Weight, net	6.5 kg 14.33 lb
Material Specifications	
Material Type	Galvanized steel
Packaging and Weights	
Included	Brackets Hardware
Packaging quantity	1
Regulatory Compliance/Certifications	

Regulatory Compliance/Certifications

Agency Clas	sification
CHINA-ROHS Belo	w maximum concentration value
ISO 9001:2015 Desi	igned, manufactured and/or distributed under this quality management system
REACH-SVHC Com	npliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS Com	npliant
UK-ROHS Com	npliant



Page 6 of 6

