



Mini-OTE 300-Series, Optical Terminal Enclosure, 4-port mini-size DLX connector, with 1x4 splitter, black, with grounding, external mounting. Splitter outputs connected to terminal housing ports, maximum 26 splices.

- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Accommodates CommScope's field installable splitters and compact CWDMs

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   EMEA   Latin America   North America |
| <b>Product Type</b>          | Access terminal, with splitter              |
| <b>Product Series</b>        | Mini-OTE 300                                |


## General Specifications

|                          |   |
|--------------------------|---|
| <b>Application</b>       | For central core tube ribbon shielded/unshielded fiber cable   For flat drop with/without trace wire fiber cable   For loose buffer tube standard (72 F) and micro (144 F) fiber cable   For round armored up to 0.50 in/12.7 mm diameter fiber cable |
| <b>Cable Type</b>        | No cable (stubless)   |
| <b>Distribution Type</b> | 1 x 4 splitter  |
| <b>Port Type</b>         | Hardened mini-size DLX  |
| <b>Port, quantity</b>    | 4   |


## Dimensions

|                           |                    |
|---------------------------|--------------------|
| <b>Height</b>             | 342.9 mm   13.5 in |
| <b>Width</b>              | 182.88 mm   7.2 in |
| <b>Depth</b>              | 121.92 mm   4.8 in |
| <b>Cable Length, stub</b> | 0 ft (0 m)         |

## Dimension Drawing



## Ordering Tree



## Optical Specifications

**Operating Wavelength Range** 1260 – 1635 nm

## Environmental Specifications

**Operating Temperature** -40 °C to +60 °C (-40 °F to +140 °F)

**Relative Humidity** 5%–100%, condensing

# 760249060 | OTE-04MX-14-EXTG03-U23

---

|                                    |   |
|------------------------------------|---|
| <b>Environmental Space</b>         | Above ground   Below ground   Buried                    |
| <b>Qualification Standard Note</b> | See test report CTR-1016 for details and exceptions     |
| <b>Qualification Standards</b>     | IEC 60529, IP68 + 2 m waterhead   Telcordia GR-771-CORE |
| <b>UV Resistance</b>               | UV stabilized   |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |



## Included Products

|                |   |  |
|----------------|---|--|
| 760242289      | - | Mini-OTE 300-Series, Optical Terminal Pole Cable Retention Kit |
| OTE-M-CABLERET |   |  |