## CAF-SCSC-L40N



#### Armored Jumper OM4SC/UPC to SC/UPC Duplex, 3.0mm LSZH, Aqua

Regional Availability	Asia   Australia/New Zealand   China   India	
Portfolio	CommScope®	
Product Type	Fiber patch cord, duplex	
General Specifications		
Connector A, quantity	2	
Color, boot A	Aqua	
Color, connector A	Beige	
Connector B, quantity	2	
Color, boot B	Aqua	
Color, connector B	Beige	
Construction Type	Armored	
Interface, Connector A	SC/UPC	
Interface, Connector B	SC/UPC	
Jacket Color	Aqua	
Polarity	Pairs, flipped	
Total Fibers, quantity	2	
Dimensions		
Cable Assembly Length Range (m)	1 – 300	
Cable Assembly Length Range (ft)	3 – 999	
Diameter Over Jacket	3 mm   0.118 in	
Mechanical Specifications		
Tensile Load, long term, maximum	200 N   44.962 lbf	
Tensile Load, short term, maximum	400 N   89.924 lbf	
Cable Retention Strength, maximum	15.43 lb @ 0°	

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 19, 2023



# CAF-SCSC-L40N

## **Optical Specifications**

Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED®
Insertion Loss, maximum	0.3 dB
Return Loss, minimum	27 dB

### **Environmental Specifications**

Operating Temperature	-25 °C to +70 °C (-13 °F to +158 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)
Qualification Standards	IEC 61753-1, category OP

### Packaging and Weights

**Packaging quantity** 

1

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 19, 2023

