

## Uniprise® Category 6 Patch Panels

### UNP610 Products

Uniprise introduces a new line of Category 6 patch panels. The UNP610 patch panels now include integrated label holders and a new rear wire management bar that can be quickly mounted directly onto the rear of the panels without any hardware. The bar can be installed from the rear of the frame or attached to the panels prior to being mounted.

The UNP610 panels are available in 12\*, 18, 24 and 48 port versions and are designed to mount into standard 19-inch racks and cabinets. The panel back consists of craft friendly color-coded gas-tight insulation displacement connections. Design features include termination options for either T568A or T568B wiring schemes.

\*12 port is a wall-mount version

### Features & Benefits

- ANSI/TIA/EIA-606-A Compliant & meets/exceeds Category 6 requirements of ISO/IEC 11801, CENELEC EN50173-1 and TIA/EIA 568B.2-1
- Integrated label holders with clear label covers and white paper labels
- Label holders accept UNJ icons in a wide array of colors and icons can be installed over each individual port
- Rear wire management bar can be quickly mounted directly onto the rear of the panels allowing the UNP610 patch panel to be mounted either in a rack or the front of a cabinet
- Applications: telecommunications rooms, equipment rooms, main cross-connects, intermediate cross-connects and data centers
- Meets and exceeds Category 6 requirements

UNP610-48P




UNP610-24P



UNP610-18P



New easy to mount rear wire management bar - provided with each panel.



UNP610-WM-12P




### Specifications

Physical Specifications	
Insertion Life:	750 cycles min.
Wire Insertion Force:	24 AWG = 13-28lbs. (58-125N)
Flammability Rating:	UL-rated 94V-0
Insulation Resistance:	500 megaohms minimum
Current Rating:	1.5A at 68°F (20°C)
Dielectric Withstand Voltage:	1000 VAC RMS, 60Hz minimum, contact-to-contact and 1500 VAC RMS, 60Hz minimum to exposed conductive surface
Listing:	UL and cUL Listed


### Catalog Number & Description

Catalog Number	Description
UNP610-WM-12P	Category 6 12 Port Wall-mount Patch Panel
UNP610-18P	Category 6 18 Port Patch Panel, 1.75" (4.45cm) H x 19.0" (48.3cm) W x 1.725" (4.38cm) D
UNP610-24P	Category 6 24 Port Patch Panel, 1.75" (4.45cm) H x 19.0" (48.3cm) W x 1.725" (4.38cm) D
UNP610-48P	Category 6 48 Port Patch Panel, 3.5" (4.45cm) H x 19.0" (48.3cm) W x 1.725" (4.38cm) D
Accessories	
UNP-CMB	Platform provides rear cable management organization and accepts the Fiber Storage Spool (UNP-FS) for multi-media applications


UNP610-WM-12P



UNP61018P



UNP610-24P



UNP610-48P

