6P-6M-A3 | V3-65A-R3



6-port sector antenna, 6x 1695–2690 MHz, 65° HPBW, 3x RET

- Uses the 4.3-10 connector which is 40 percent smaller than the 7-16 DIN connector
- With tilt indicators and integrated pluggable RET
- Utilizes RET-PMOD-A20-3A01
- Conforms to RoHS 2011/65/EU

General Specifications

| Antenna Type | Sector |
|----------------------------------|--|
| Band | Single band |
| Color | Light Gray (RAL 7035) |
| Grounding Type | RF connector inner conductor and body grounded to reflector and mounting bracket |
| Radome Material | Fiberglass, UV resistant |
| Radiator Material | Aluminum |
| Reflector Material | Aluminum |
| RF Connector Interface | 4.3-10 Female |
| RF Connector Location | Bottom |
| RF Connector Quantity, high band | 6 |
| RF Connector Quantity, total | 6 |

Remote Electrical Tilt (RET) Information

| RET Hardware | CommRET v2 |
|---|--|
| RET Interface | 2x 8 pin connector as per IEC 60130-9 Daisy chain in: Male / Daisy chain out: Female Pin3: RS485A(AISG_B), Pin5: RS485B(AISG_A), Pin6: DC 10~30V, Pin7: DC_ Return |
| RET Interface, quantity | 1 female 1 male |
| Input Voltage | 10-30 Vdc |
| Internal RET | High band (3) |
| Power Consumption, active state, maximum | 10 W |
| Power Consumption, idle state, maximum | 2 W |
| Power Consumption, normal conditions, maximum | 10 W |
| Protocol | 3GPP/AISG 2.0 (Single RET) |


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

COMMSCOPE°

Dimensions

| Width | 377 mm 14.843 in |
|----------------------------------|---------------------|
| Depth | 87 mm 3.425 in |
| Length | 1397 mm 55 in |
| Net Weight, without mounting kit | 15.5 kg 34.172 lb |

Array Layout



| Array ID | Frequency (MHz) | RF Connector | RET (SRET) | AISG RET UID |
|----------|-----------------|--------------|---------------|---|
| Y1 | 1695-2690 | 1 - 2 | 1 | CPxxxxxxxxxxxxxXXXXXY1 |
| Y2 | 1695-2690 | 3 - 4 | 2 | CPxxxxxxxxxxxxXXXXXXXXXXXXXXXXXXXXXXXXX |
| Y3 | 1695-2690 | 5 - 6 | 3 | CPxxxxxxxxxxxxxXXXXXXXXXXXXXXXXXXXXXXXX |

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Page 2 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024



6P-6M-A3 | V3-65A-R3

Electrical Specifications

| Impedance | 50 ohm |
|----------------------------|-----------------|
| Operating Frequency Band | 1695 – 2690 MHz |
| Polarization | ±45° |
| Total Input Power, maximum | 600 W |

Electrical Specifications

| Frequency Band, MHz | 1695-1880 | 1850-1990 | 1920-2200 | 2300-2500 | 2500-2690 |
|---|------------|------------|------------|------------|------------|
| Gain, dBi | 17.1 | 17.5 | 17.9 | 18.3 | 18.2 |
| Beamwidth, Horizontal, degrees | 67 | 65 | 63 | 59 | 58 |
| Beamwidth, Vertical, degrees | 7.2 | 6.9 | 6.4 | 5.5 | 5.3 |
| Beam Tilt, degrees | 2-12 | 2-12 | 2-12 | 2-12 | 2-12 |
| USLS (First Lobe), dB | 19 | 21 | 19 | 18 | 20 |
| Isolation, Cross Polarization, dB | 28 | 28 | 28 | 28 | 28 |
| Isolation, Inter-band, dB | 28 | 28 | 28 | 28 | 28 |
| VSWR Return loss, dB | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 |
| PIM, 3rd Order, 2 x 20 W, dBc | -150 | -150 | -150 | -150 | -150 |
| Input Power per Port, maximum, watts | 250 | 250 | 250 | 250 | 250 |
| Input Total Power per Antenna at 50°C, maximum, watts | 250 | 250 | 250 | 250 | 250 |

Electrical Specifications, BASTA

| Frequency Band, MHz | 1695-1880 | 1850-1990 | 1920-2200 | 2300-2500 | 2500-2690 |
|---|-----------|-----------|-----------|-----------|-----------|
| Gain by all Beam Tilts, average, dBi | 16.8 | 17.3 | 17.6 | 17.9 | 17.7 |
| Gain by all Beam Tilts Tolerance, dB | ±0.6 | ±0.4 | ±0.4 | ±0.6 | ±0.7 |
| Beamwidth, Horizontal Tolerance, degrees | ±4.8 | ±2.8 | ±4.2 | ±3.7 | ±3.9 |
| Beamwidth, Vertical Tolerance, degrees | ±0.4 | ±0.4 | ±0.6 | ±0.5 | ±0.4 |
| Front-to-Back Total Power at 180° ± 30°, dB | 25 | 28 | 28 | 28 | 27 |
| CPR at Boresight, dB | 24 | 26 | 26 | 25 | 24 |

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024



6P-6M-A3 | V3-65A-R3

| 11 | 12 | | 12 | 7 | 6 |
|-------|-------------|-------------|--|---|--|
| tions | | | | | |
| | | 524.0 N @ 1 | 50 km/h (117.8 lbf (| @ 150 km/h) | |
| | | 58.0 N @ 15 | 50 km/h (13.0 lbf @ | 150 km/h) | |
| | | 482.0 N @ 1 | 50 km/h (108.4 lbf (| @ 150 km/h) | |
| | | 241 km/h (1 | 50 mph) | | |
| | 11 tions | tions | tions 524.0 N @ 1 58.0 N @ 15 482.0 N @ 1 | tions 524.0 N @ 150 km/h (117.8 lbf 58.0 N @ 150 km/h (13.0 lbf @ | tions 524.0 N @ 150 km/h (117.8 lbf @ 150 km/h) 58.0 N @ 150 km/h (13.0 lbf @ 150 km/h) 482.0 N @ 150 km/h (108.4 lbf @ 150 km/h) |

Packaging and Weights

| Width, packed | 472 mm 18.583 in |
|----------------|---------------------|
| Depth, packed | 207 mm 8.15 in |
| Length, packed | 1627 mm 64.055 in |
| Weight, gross | 23 kg 50.706 lb |
| Weight, net | 15.5 kg 34.172 lb |
| | |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CE | Compliant with the relevant CE product directives |
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |
| CE | |

Included Products

BSAMNT-B95-03

Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

