

PLUG-12



Cushion Plugs for 1/2 in corrugated coaxial cable

Product Classification

Product Type	Cushion plug
Ordering Note	CommScope® non-standard product

General Specifications

Cable Type	Corrugated
Color	Black

Dimensions

Length	3 in 76.2 mm
Nominal Size	1/2 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Environmental Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	≥1000 hours
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66

Packaging and Weights

Height, packed	12 in 304.8 mm
Width, packed	11 in 279.4 mm
Length, packed	1 in 25.4 mm
Included	Five plugs
Packaging quantity	5
Weight, gross	0.06 kg 0.132 lb

PLUG-12

Regulatory Compliance/Certifications

Agency**Classification**

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

