


# MC-DPM2M-6-B



Monopole Co-location Dual Pipe Mount Base Kit, 12 in to 50 in OD, 4 ft 9 in face, pipe ordered separately

## Product Classification

**Product Type** Co-location dual pipe mount kit

## General Specifications

**Mounting** Monopole, 304.8–1270 mm (12–50 in) OD

**Pipe, quantity** 0

**Sectors, quantity** 3

## Dimensions

**Height** 254 mm | 10 in

**Face Width** 1.463 m | 4.8 ft

**Width** 1,447.8 mm | 57 in

**Length** 355.6 mm | 14 in

**Mounting Diameter, maximum** 1270 mm | 50 in

**Mounting Diameter, minimum** 304.8 mm | 12 in

**Pipe Outer Diameter** 60.96 mm | 2.4 in

**Stand-off Distance** 355.6 mm | 14 in

**Mounting Circumference, maximum** 3,990.34 mm | 157.1 in

**Mounting Circumference, minimum** 1,196.34 mm | 47.1 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

**Wind Rating Criteria** Two 72 in x 8 in panel antennas per sector

**Wind Rating Test Method** TIA/EIA-222-G

# MC-DPM2M-6-B

---

## Packaging and Weights

<b>Included</b>	Dual pipe frames   Pipe mounts   Ring mount
<b>Packaging quantity</b>	1
<b>Weight, net</b>	247.208 kg   545 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--