

760256443 | TENIO-B6-START



TENIO™ B6 144f Distribution closure STARTer kit with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

Suitable for all splice closure applications with a maximum capacity of 144 fibres. This basic kit contains a full set of blanking seals, one-feeder cable seal kit, cable termination units to install a loop-through feeder. Full set of splice trays for up to 144f splices. Please select distribution seal kits, CTU's and splitters from our ordering guide. This kit contains a MOBRA bracket suitable for use with PIA chambers. Fibre trays and seal kits are pre-assembled into the closure in the factory to reduce engineering time in the field.

Product Classification

Regional Availability	EMEA Latin America
Product Type	Single-ended, rectangular fiber closure
Product Brand	TENIO™
Product Series	TENIO

General Specifications

Cable Entry Drop Port Style	Gel block
Cable Entry Main Port Style	Gel block
Cable Ports Quantity, total	6 multi-out ports (30 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Side latch
Closure Style	Single-ended
Color	Black
Flash Test Valve	Pre-installed
Mounting	Wall
Network Area Type	Distribution Drop
Splice Tray Included, quantity	0
Splice Tray Type Included	12-fiber, single element
Splices per Tray, quantity	12
Splicing Capacity, Single Fusion, maximum	144
Splicing Type, Supported	Single fusion

760256443 | TENIO-B6-START

Dimensions

Height	230 mm 9.055 in
Width	134 mm 5.276 in
Length	389 mm 15.315 in
Main Cable Diameter, maximum	16 mm 0.63 in

Material Specifications

Material Type	Impact-resistant polymer
----------------------	--------------------------

Environmental Specifications

Environmental Space	Below ground Buried
Qualification Standards	IEC 61300, 2 m waterhead
Water Resistance	Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity	1
Packaging Type	Box Carton
Weight, net	1 kg 2.205 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

760244933 CTU-L	-	Fiber Closure Cable Termination Unit, Large for up to 16 mm diameter cables
760250714 TENIO-MOBRA-TUBE-45x45	-	TENIO™ Mounting bracket for arm mounting
CV6797-000 TENIO-SKG3-7/10	-	TENIO™ Cable Gel Seal kit, 3 cable outlets, 7 to 10 mm diameter per cable outlet
CV6800-000 TENIO-B6-S12-12-V	-	TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, 12 pre-installed 12-fiber trays, 12 heat shrink splice protectors (SMOUV 45 mm), with test valve

760256443 | TENIO-B6-START

CW8862-000
TENIO-SKG-DUMMY

- TENIO™ Cable Gel Seal kit, dummy, no cable outlets, black