

SSH-47



SnapTak PIM-Guard Adjustable Hanger for 4.0 mm to 7.0 mm Cable – PIM Free Polymer Construction. No Grommets Required

OBSOLETE

Replaced By:

SSH-411

SnapTak PIM-Guard Adjustable Hanger, Gen 2. Fits 4.0 mm to 11.0 mm Cables – PIM Free Polymer Construction. No Grommets Required

Product Classification

Product Type	Hanger kit
Product Brand	SnapTak PIM-Guard
Ordering Note	CommScope® standard product (Global)

General Specifications

Accessories	Hangers
Cables per Hanger	1
Color	Black
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	3
Maximum Stack Height, Coaxial	3
Height	27.2 mm 1.071 in
Width	32 mm 1.26 in
Length	32 mm 1.26 in
Compatible Cable Diameter Range	4–7 mm
Compatible Diameter, maximum	7 mm 0.276 in
Compatible Diameter, minimum	4 mm 0.157 in

Electrical Specifications

SSH-47

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
---------------------------	--------------------------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	3.1 cm 1.22 in
Width, packed	20.3 cm 7.992 in
Length, packed	25.4 cm 10 in
Packaging quantity	10
Weight, gross	0.54 kg 1.19 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power