

# NNVSSP-360S-FM



14-port quasi-omni antenna, 4x 698–896, 4x 1695–2690, 4x 3400–3800 and 2x 5150–5925 MHz, 360° horizontal beamwidth. Fixed and manual tilt.

## Electrical Specifications

Frequency Band, MHz	698–806	806–896	1695–1920	1920–2180	2300–2690	3400–3800	5150–5925
Gain, dBi	4.8	4.6	6.1	6.6	7.5	5.7	4.0
Beamwidth, Horizontal, degrees	360	360	360	360	360	360	360
Beamwidth, Vertical, degrees	62.3	55.1	19.2	16.9	14.3	38.2	20.9
Beam Tilt, degrees	0	0	5–15	5–15	5–15	0	0
Isolation, Cross Polarization, dB	25	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25	25
VSWR   Return Loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-150		
Input Power per Port at 50°C, maximum, watts	75	75	75	75	75		
Polarization	±45°	±45°	±45°	±45°	±45°	±45°	±45°
Impedance	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm

## Electrical Specifications, BASTA\*

Frequency Band, MHz	698–806	806–896	1695–1920	1920–2180	2300–2690	3400–3800	5150–5925
Gain by all Beam Tilts, average, dBi	4.6	4.3	5.5	6.1	7.0	5.3	3.2
Gain by all Beam Tilts Tolerance, dB	±0.4	±0.4	±1	±0.5	±0.9	±0.8	±0.9
Gain by Beam Tilt, average, dBi			5 °   5.7 10 °   5.6 15 °   5.4	5 °   6.0 10 °   6.2 15 °   6.1	5 °   7.2 10 °   7.1 15 °   6.9		
Beamwidth, Vertical Tolerance, degrees	±12.9	±12.3	±2.4	±1.6	±1.6	±5.5	±5.3

\* CommScope® supports NGMN recommendations on Base Station Antenna Standards (BASTA). To learn more about the benefits of BASTA, [download the whitepaper Time to Raise the Bar on BSAs](#).

## 5 GHz Port Power Table

5 GHz FCC Power Requirements				
U-NII Band	U-NII 1	U-NII 2A	U-NII 2C	U-NII 3
Frequency (MHz)	5150 - 5250	5250 - 5350	5470 - 5725	5725 - 5850
Max Input power per port to align with FCC Title 47 Part 15 (Watts)	0.5	0.125	0.125	0.5

## Port Configuration



## General Specifications

**Operating Frequency Band**      1695 – 2690 MHz | 3400 – 3800 MHz | 5150 – 5925 MHz | 698 – 896 MHz

# NNVSSP-360S-FM

---

<b>Antenna Type</b>	Small Cell
<b>Band</b>	Multiband
<b>Performance Note</b>	Outdoor usage

## Mechanical Specifications

<b>RF Connector Quantity, total</b>	14
<b>RF Connector Quantity, low band</b>	4
<b>RF Connector Quantity, high band</b>	10
<b>RF Connector Interface</b>	4.3-10 Female
<b>Grounding Type</b>	RF connector inner conductor and body grounded to reflector and mounting bracket
<b>Radiator Material</b>	Aluminum   Low loss circuit board
<b>Radome Material</b>	ASA, UV stabilized
<b>Reflector Material</b>	Aluminum
<b>RF Connector Location</b>	Bottom
<b>Wind Loading, frontal</b>	122.0 N @ 150 km/h 27.4 lbf @ 150 km/h
<b>Wind Loading, maximum</b>	122.0 N @ 150 km/h 27.4 lbf @ 150 km/h
<b>Wind Speed, maximum</b>	241 km/h   150 mph

## Dimensions

<b>Length</b>	730.0 mm   28.7 in
<b>Outer Diameter</b>	305.0 mm   12.0 in
<b>Net Weight, without mounting kit</b>	12.1 kg   26.7 lb

## Packed Dimensions

<b>Length</b>	1000.0 mm   39.4 in
<b>Width</b>	418.0 mm   16.5 in
<b>Depth</b>	404.0 mm   15.9 in
<b>Shipping Weight</b>	16.7 kg   36.8 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)



## \* Footnotes

### **Performance Note**

Severe environmental conditions may degrade optimum performance