



2RU patch panel which interfaces with MPO-8 ports including QSFP to easily break them out into LC connections. The MPO and shuttered LC ports are both front facing for easy mapping and patching. 20 singlemode MPO-8 and 80 duplex LC ports, Enhanced Method B

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Depth</b>	292.10 mm   11.50 in
<b>Height</b>	82.55 mm   3.25 in
<b>Width</b>	482.60 mm   19.00 in

## Environmental Specifications

<b>Safety Standard</b>	UL 60950
------------------------	----------

## General Specifications

<b>Rack Units</b>	2.0
<b>Shelf Movement</b>	Fixed
<b>Color, front</b>	Blue   Gray
<b>Interface Feature, front</b>	LC/UPC   MPO
<b>Interface, front</b>	MPO Pinned
<b>Package Quantity</b>	1
<b>Total Ports, quantity, front</b>	80

## Optical Performance

<b>Insertion Loss, maximum</b>	0.60 dB
--------------------------------	---------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

