



OFDC B8 Fiber Optic Splice Closure, Gel Cable sealing, 2 pre-installed 36-fiber splice trays, no splitters

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and separate zones for looped cable storage for most cable types
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

Product Classification

Product Type	Single-ended, rectangular fiber closure
Regional Availability	Asia EMEA Latin America
Product Series	OFDC

General Specifications

Splicing Type, Supported	Single fusion
Enclosure Color	Black
Package, quantity	1
Packaging Type	Box Carton
Splice Protector Length, maximum	45.00 mm 1.77 in
Splice Tray Included, quantity	2
Splice Tray Type Included	36-way, heat shrink
Splicing Capacity, maximum	72

Dimensions

Height	163.00 mm 6.42 in
Length	326.00 mm 12.83 in
Weight	1.85 kg 4.08 lb
Width	102.00 mm 4.02 in

Mechanical Specifications

Cable Sealing Type	Compressed gel
Enclosure Material Type	Rugged polymer
Mount Type	Manhole Pedestal Strand Wall

Environmental Specifications

Environmental Space	Above ground Below ground
----------------------------	-----------------------------

Installation Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Qualification Standard	IEC 60529, IP68 + 2 m waterhead
Relative Humidity	93%, non-condensing
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
UV Resistance	UV stabilized

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

