


LazrSPEED® Indoor/Outdoor Low Smoke Zero Halogen Single Jacket All-Dielectric Arid-Core Drop Cable



Product Classification


| | |
|------------------------------|---|
| Portfolio | CommScope® |
| Product Type | Fiber drop cable |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Standards And Qualifications

| | |
|--------------------------------------|---------------------|
| EN50575 CPR Cable EuroClass | Dca s2 d1 a1 |
| Cable Qualification Standards | ANSI/ICEA S-110-717 |

Representative Image

16-Fiber Cable Shown



General Specifications

| | |
|--------------------------|-----------------------|
| Cable Type | Riser rated low smoke |
| Construction Type | Non-armored |
| Subunit Type | Gel-filled |

Construction Materials

| | |
|-------------------------------------|-------------------------------|
| Fiber Type Solution | OM3, LazrSPEED® 300 |
| Jacket Material | Low Smoke Zero Halogen (LSZH) |
| Total Fiber Count | 12 |
| Fiber Type | OM3, LazrSPEED® 300 |
| Fiber Type, quantity | 12 |
| Fibers per Subunit, quantity | 12 |
| Jacket Color | Black |
| Jacket UV Resistance | UV stabilized |

Dimensions

| | |
|-------------------------------------|--------------------------|
| Buffer Tube/Subunit Diameter | 4.00 mm 0.16 in |
| Cable Weight | 48.0 lb/kft 72.0 kg/km |
| Diameter Over Jacket | 8.30 mm 0.33 in |
| Subunit, quantity | 1 |

Physical Specifications

| | |
|--|---------------------|
| Minimum Bend Radius, loaded | 12.5 cm 4.9 in |
| Minimum Bend Radius, unloaded | 8.3 cm 3.3 in |
| Tensile Load, long term, maximum | 400 N 90 lbf |
| Tensile Load, short term, maximum | 1334 N 300 lbf |
| Vertical Rise, maximum | 572.0 m 1876.6 ft |

Flame Test Specifications

| | |
|--------------------------|--|
| Flame Test Method | IEC 60332-3 IEC 60754-2 IEC 61034-2 IEEE 383 UL 1666 UL 1685 |
|--------------------------|--|

Environmental Specifications

| | |
|---------------------------------|---|
| Environmental Space | Aerial, lashed Buried Low Smoke Zero Halogen (LSZH) Riser |
| Installation Temperature | -20 °C to +60 °C (-4 °F to +140 °F) |
| Operating Temperature | -20 °C to +70 °C (-4 °F to +158 °F) |
| Storage Temperature | -20 °C to +75 °C (-4 °F to +167 °F) |

Mechanical Test Specifications

| | |
|--------------------------------|---------------------------|
| Compression | 10 N/mm 57 lb/in |
| Compression Test Method | FOTP-41 IEC 60794-1 E3 |
| Flex | 35 cycles |
| Flex Test Method | FOTP-104 IEC 60794-1 E6 |
| Impact | 2.17 ft lb 2.94 N-m |
| Impact Test Method | FOTP-25 IEC 60794-1 E4 |

| | |
|--------------------------------------|---------------------------------------|
| Strain | See long and short term tensile loads |
| Strain Test Method | FOTP-33 IEC 60794-1 E1 |
| Twist | 10 cycles |
| Twist Test Method | FOTP-85 IEC 60794-1 E7 |
| Water Penetration | 24 h |
| Water Penetration Test Method | FOTP-82 IEC 60794-1 F5 |

Environmental Test Specifications

| | |
|--------------------------------------|-------------------------------------|
| Cable Freeze | -2 °C 28 °F |
| Cable Freeze Test Method | FOTP-98 IEC 60794-1 F15 |
| Drip | 70 °C 158 °F |
| Drip Test Method | FOTP-81 IEC 60794-1 E14 |
| Heat Age Test Method | IEC 60794-1 F9 |
| Low High Bend | -20 °C to +60 °C (-4 °F to +140 °F) |
| Low High Bend Test Method | FOTP-37 IEC 60794-1 E11 |
| Temperature Cycle | -20 °C to +70 °C (-4 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3 IEC 60794-1 F1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|--|
| RoHS 2011/65/EU | Compliant |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| CENELEC | EN 50575 compliant, Declaration of Performance (DoP) available |



Included Products

CS-5L-LT (Product Component—not orderable) — LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

LazrSPEED® 300

Product Classification

| | |
|------------------------------|---|
| Portfolio | CommScope® |
| Product Type | Optical fiber |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Optical Specifications, Wavelength Specific

| | |
|-------------------------------------|--|
| Standards Compliance | TIA-492AAAC (OM3) |
| Attenuation, maximum | 1.00 dB/km @ 1300 nm 3.00 dB/km @ 850 nm |
| Differential Mode Delay Note | Superior to TIA-492AAAC and IEC 60793-2-10 at 850 nm |
| Index of Refraction | 1.479 @ 1300 nm 1.483 @ 850 nm |
| 1 Gbps Ethernet Distance | 600 m @ 1300 nm 1020 m @ 850 nm |
| 10 Gbps Ethernet Distance | 300 m @ 850 nm 984 ft @ 850 nm |
| Bandwidth, Laser, minimum | 500 MHz-km @ 1300 nm 2000 MHz-km @ 850 nm |
| Bandwidth, OFL, minimum | 500 MHz-km @ 1300 nm 1500 MHz-km @ 850 nm |
| Differential Mode Delay | 0.70 ps/m @ 850 nm 0.88 ps/m @ 1300 nm |
| Backscatter Coefficient | -75.7 dB @ 1300 nm -68.0 dB @ 850 nm |

Physical Specifications

| | |
|--|----------|
| Cladding Diameter | 125.0 µm |
| Cladding Diameter Tolerance | ±1.0 µm |
| Cladding Non-Circularity, maximum | 1.0 % |
| Coating Diameter (Colored) | 254 µm |
| Coating Diameter (Uncolored) | 245 µm |
| Coating Diameter Tolerance (Colored) | ±7 µm |
| Coating Diameter Tolerance (Uncolored) | ±10 µm |
| Coating/Cladding Concentricity Error, maximum | 12 µm |
| Core Diameter | 50.0 µm |
| Core Diameter Tolerance | ±2.5 µm |
| Core/Clad Offset, maximum | 1.5 µm |

Optical Specifications, General

| | |
|--|---------------------|
| Numerical Aperture | 0.200 |
| Numerical Aperture Tolerance | ±0.015 |
| Point Defects, maximum | 0.15 dB |
| Zero Dispersion Slope, maximum | 0.105 ps/[km-nm-nm] |
| Zero Dispersion Wavelength, maximum | 1316 nm |
| Zero Dispersion Wavelength, minimum | 1297 nm |

Mechanical Specifications

| | |
|---|--|
| Coating Strip Force, maximum | 8.9 N 2.0 lbf |
| Coating Strip Force, minimum | 1.3 N 0.3 lbf |
| Dynamic Fatigue Parameter, minimum | 18 |
| Macrobending, 15 mm mandrel, 2 turns | 0.20 dB @ 850 nm 0.50 dB @ 1300 nm |
| Macrobending, 30 mm mandrel, 2 turns | 0.10 dB @ 850 nm 0.30 dB @ 1300 nm |
| Macrobending, 75 mm mandrel, 100 turns | 0.50 dB @ 850 nm 0.50 dB @ 1300 nm |
| Proof Test | 689.48 N/mm ² 100000.00 psi |

Environmental Specifications

| | |
|--|--------------------|
| Heat Aging, maximum | 0.20 dB/km @ 85 °C |
| Temperature Dependence, maximum | 0.10 dB/km |
| Temperature Humidity Cycling, maximum | 0.20 dB/km |
| Water Immersion, maximum | 0.20 dB/km @ 23 °C |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



* Footnotes

| | |
|--|---|
| Temperature Dependence, maximum | Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F) |
| Temperature Humidity Cycling, maximum | Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity |