

LazrSPEED® Low Smoke Zero Halogen Riser Distribution Cable, 72 fiber multi-unit with 12 fiber subunits


Product Classification

Portfolio	CommScope®
Product Type	Fiber indoor cable
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Standards And Qualifications

EN50575 CPR Cable EuroClass	Cca s1b d1 a1
Cable Qualification Standards	ANSI/CEA S-83-596 Telcordia GR-409

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	OM3, LazrSPEED® 300
Total Fiber Count	72
Fiber Type	OM3, LazrSPEED® 300

Fiber Type, quantity	72
Fibers per Subunit, quantity	12
Jacket Color	Aqua

Dimensions

Buffer Tube/Subunit Diameter	6.07 mm 0.24 in
Cable Weight	360.0 kg/km
Diameter Over Jacket	20.01 mm 0.79 in
Subunit, quantity	6

Physical Specifications

Minimum Bend Radius, loaded	300.0 mm 11.8 in
Minimum Bend Radius, unloaded	200.0 mm 7.9 in
Tensile Load, long term, maximum	400 N 90 lbf
Tensile Load, short term, maximum	1335 N 300 lbf
Vertical Rise, maximum	113.0 m 370.7 ft

Flame Test Specifications

Flame Test Listing	NEC OFNR-LS (ETL) and c(ETL)
Flame Test Method	IEC 60332-3 IEC 60754-2 IEC 61034-2 IEEE 383 UL 1666 UL 1685

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH) Riser
Installation Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression	10 N/mm
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	100 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	5.88 N-m 4.34 ft lb
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-10 °C to +60 °C (+14 °F to +140 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available



Included Products

CS-5L-TB (Product Component—not orderable) — LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable