

LazrSPEED® Indoor/Outdoor Low Smoke Zero Halogen Single Jacket All-Dielectric Arid-Core Drop Cable


## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber drop cable
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Standards And Qualifications

<b>EN50575 CPR Cable EuroClass</b>	Dca   s2   d1   a1
<b>Cable Qualification Standards</b>	ANSI/ICEA S-110-717   EN 187105   Telcordia GR-409

## Representative Image



## General Specifications

<b>Cable Type</b>	Riser rated low smoke
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled

## Construction Materials

<b>Fiber Type Solution</b>	OM3, LazrSPEED® 300
<b>Jacket Material</b>	Low Smoke Zero Halogen (LSZH)
<b>Total Fiber Count</b>	12
<b>Fiber Type</b>	OM3, LazrSPEED® 300
<b>Fiber Type, quantity</b>	12
<b>Fibers per Subunit, quantity</b>	12
<b>Jacket Color</b>	Black
<b>Jacket UV Resistance</b>	UV stabilized

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	2.00 mm   0.08 in
<b>Cable Weight</b>	30.0 lb/kft   44.0 kg/km
<b>Diameter Over Jacket</b>	6.10 mm   0.24 in
<b>Subunit, quantity</b>	1

## Physical Specifications

<b>Minimum Bend Radius, loaded</b>	9.1 cm   3.6 in
<b>Minimum Bend Radius, unloaded</b>	6.1 cm   2.4 in
<b>Tensile Load, long term, maximum</b>	400 N   90 lbf
<b>Tensile Load, short term, maximum</b>	1334 N   300 lbf
<b>Vertical Rise, maximum</b>	927.0 m   3041.3 ft

## Flame Test Specifications

<b>Flame Test Listing</b>	NEC OFNR-LS (ETL) and c(ETL)
<b>Flame Test Method</b>	IEC 60332-3   IEC 60754-2   IEC 61034-2   IEEE 383   UL 1666   UL 1685

## Environmental Specifications

<b>Environmental Space</b>	Aerial, lashed   Buried   Low Smoke Zero Halogen (LSZH)   Riser
<b>Installation Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)

## Mechanical Test Specifications

<b>Compression</b>	10 N/mm   57 lb/in
<b>Compression Test Method</b>	FOTP-41   IEC 60794-1 E3
<b>Flex</b>	35 cycles
<b>Flex Test Method</b>	FOTP-104   IEC 60794-1 E6
<b>Impact</b>	1.63 ft lb   2.21 N-m

<b>Impact Test Method</b>	FOTP-25   IEC 60794-1 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	FOTP-33   IEC 60794-1 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	FOTP-85   IEC 60794-1 E7
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	FOTP-82   IEC 60794-1 F5

## Environmental Test Specifications

<b>Cable Freeze</b>	-2 °C   28 °F
<b>Cable Freeze Test Method</b>	FOTP-98   IEC 60794-1 F15
<b>Drip</b>	70 °C   158 °F
<b>Drip Test Method</b>	FOTP-81   IEC 60794-1 E14
<b>Heat Age Test Method</b>	IEC 60794-1 F9
<b>Low High Bend</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Low High Bend Test Method</b>	FOTP-37   IEC 60794-1 E11
<b>Temperature Cycle</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	FOTP-3   IEC 60794-1 F1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available



## Included Products

CS-5L-LT (Product Component—not orderable) — LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber

LazrSPEED® 300

Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Optical fiber
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

Optical Specifications, Wavelength Specific

<b>Standards Compliance</b>	TIA-492AAAC (OM3)
<b>Attenuation, maximum</b>	1.00 dB/km @ 1300 nm 3.00 dB/km @ 850 nm
<b>Differential Mode Delay Note</b>	Superior to TIA-492AAAC and IEC 60793-2-10 at 850 nm
<b>Index of Refraction</b>	1.479 @ 1300 nm 1.483 @ 850 nm
<b>1 Gbps Ethernet Distance</b>	600 m @ 1300 nm 1020 m @ 850 nm
<b>10 Gbps Ethernet Distance</b>	300 m @ 850 nm 984 ft @ 850 nm
<b>Bandwidth, Laser, minimum</b>	500 MHz-km @ 1300 nm 2000 MHz-km @ 850 nm
<b>Bandwidth, OFL, minimum</b>	500 MHz-km @ 1300 nm 1500 MHz-km @ 850 nm
<b>Differential Mode Delay</b>	0.70 ps/m @ 850 nm 0.88 ps/m @ 1300 nm
<b>Backscatter Coefficient</b>	-75.7 dB @ 1300 nm -68.0 dB @ 850 nm

Physical Specifications

<b>Cladding Diameter</b>	125.0 µm
<b>Cladding Diameter Tolerance</b>	±1.0 µm
<b>Cladding Non-Circularity, maximum</b>	1.0 %
<b>Coating Diameter (Colored)</b>	254 µm
<b>Coating Diameter (Uncolored)</b>	245 µm
<b>Coating Diameter Tolerance (Colored)</b>	±7 µm
<b>Coating Diameter Tolerance (Uncolored)</b>	±10 µm
<b>Coating/Cladding Concentricity Error, maximum</b>	12 µm
<b>Core Diameter</b>	50.0 µm
<b>Core Diameter Tolerance</b>	±2.5 µm
<b>Core/Clad Offset, maximum</b>	1.5 µm

## Optical Specifications, General

<b>Numerical Aperture</b>	0.200
<b>Numerical Aperture Tolerance</b>	±0.015
<b>Point Defects, maximum</b>	0.15 dB
<b>Zero Dispersion Slope, maximum</b>	0.105 ps/[km-nm-nm]
<b>Zero Dispersion Wavelength, maximum</b>	1316 nm
<b>Zero Dispersion Wavelength, minimum</b>	1297 nm

## Mechanical Specifications

<b>Coating Strip Force, maximum</b>	8.9 N   2.0 lbf
<b>Coating Strip Force, minimum</b>	1.3 N   0.3 lbf
<b>Dynamic Fatigue Parameter, minimum</b>	18
<b>Macrobending, 15 mm mandrel, 2 turns</b>	0.20 dB @ 850 nm 0.50 dB @ 1300 nm
<b>Macrobending, 30 mm mandrel, 2 turns</b>	0.10 dB @ 850 nm 0.30 dB @ 1300 nm
<b>Macrobending, 75 mm mandrel, 100 turns</b>	0.50 dB @ 850 nm 0.50 dB @ 1300 nm
<b>Proof Test</b>	689.48 N/mm <sup>2</sup>   100000.00 psi

## Environmental Specifications

<b>Heat Aging, maximum</b>	0.20 dB/km @ 85 °C
<b>Temperature Dependence, maximum</b>	0.10 dB/km
<b>Temperature Humidity Cycling, maximum</b>	0.20 dB/km
<b>Water Immersion, maximum</b>	0.20 dB/km @ 23 °C

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



### \* Footnotes

<b>Temperature Dependence, maximum</b>	Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
<b>Temperature Humidity Cycling, maximum</b>	Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity