

Fiber Optic Cable, 4-fiber, OM2, 2000 m, orange

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber indoor/outdoor cable
Regional Availability	Asia Australia/New Zealand EMEA

Standards And Qualifications

EN50575 CPR Cable EuroClass	Eca
------------------------------------	-----

Optical Specifications, Wavelength Specific

Attenuation, maximum	0.70 dB/km @ 1300 nm 3.50 dB/km @ 850 nm
Standards Compliance	TIA-492AAAB (OM2)

General Specifications

Cable Type	Loose tube
Subunit Type	Gel-filled

Construction Materials

Total Fiber Count	4
Fiber Type	OM2
Fibers per Subunit, quantity	4
Jacket Color	Orange

Dimensions

Cable Length	2000 m 6562 ft
Cable Weight	48.0 kg/km
Diameter Over Jacket	6.40 mm 0.25 in

Physical Specifications

Minimum Bend Radius, loaded	130.0 mm 5.1 in
Minimum Bend Radius, unloaded	80.0 mm 3.1 in
Tensile Load, long term, maximum	650 N 146 lbf
Tensile Load, short term, maximum	1250 N 281 lbf

Environmental Specifications

2-599622-7

Environmental Space Universal Low Smoke Zero Halogen (ULSZH)
Operating Temperature -20 °C to +70 °C (-4 °F to +158 °F)

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU CENELEC	Compliant EN 50575 compliant, Declaration of Performance (DoP) available



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable