

Outside Plant Fiber Optic Cable, armored, 8-fiber, SM, OS2, loose tube, gel-filled, 1000 m

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber OSP cable
Regional Availability	Asia

Optical Specifications, Wavelength Specific

Standards Compliance	ANSI/TIA-568.A TIA-492CAAB (OS2)
-----------------------------	------------------------------------

General Specifications

Cable Type	Loose tube
Subunit Type	Gel-filled

Construction Materials

Total Fiber Count	8
Armor Type	Corrugated steel
Fiber Type	OS2
Fibers per Subunit, quantity	8
Jacket Color	Black

Dimensions

Cable Length	1000 m 3281 ft
Cable Weight	108.0 kg/km
Diameter Over Jacket	10.30 mm 0.41 in

Physical Specifications

Minimum Bend Radius, loaded	206.0 mm 8.1 in
Tensile Load, long term, maximum	890 N 200 lbf
Tensile Load, short term, maximum	2700 N 607 lbf

Environmental Specifications

Installation Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable