




ETL Verified Category 5e U/UTP Cable, non-plenum, white jacket, 4 pair count, 1000 ft (305 m) length, CommPak

Product Classification

Portfolio	CommScope®
Product Type	Twisted pair cable
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Cross Section Drawing



Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Insulation Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	18.80 lb/kft
Diameter Over Jacket, nominal	4.953 mm 0.195 in
Jacket Thickness	0.508 mm 0.020 in

Electrical Specifications

ANSI/TIA Category	5e
Characteristic Impedance	100 ohm

dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m
Delay Skew, maximum	15 ns
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	200 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-3-1 ISO/IEC 11801 Class D
Safety Voltage Rating	300 V
Dielectric Strength, minimum	1500 Vac 2500 Vdc
Note	All electrical transmission tests include swept frequency measurements

Environmental Specifications

Environmental Space	Non-plenum
Flame Test Method	CMR NEC Article 800 UL 1666 UL 444
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Packaging Type	CommPak® box
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	White
Product Number	CS24R
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Mechanical Specifications

Pulling Tension, maximum	11 kg 25 lb
---------------------------------	---------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Electrical Performance

CS CommScope
 Std Refers to the standard value listed under Transmission Standards in the Electrical Specifications above
 Typ Typical
 IL Insertion Loss (dB/100m)
 NEXT Near End Crosstalk (dB/100m)
 ACR Attenuation to Crosstalk Ratio (dB/100m)
 PSNEXT Power Sum Near End Crosstalk (db/100m)
 PSACR Power Sum Attenuation to Crosstalk Ratio (dB/100m)
 ACRF Attenuation to Crosstalk Ratio - Far End (dB/100m)
 PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)
 RL Return Loss (dB)

Freq. MHz	IL			NEXT			ACR			PSNEXT			PSACR			ACRF			PSACRF			RL		
	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ
1	2.0	2.0	2.1	65.3	65.3	81.5	63.3	63.3	79.4	62.3	62.3	79.2	60.3	60.3	77.1	63.8	63.8	76.4	60.8	60.8	74.7	20.0	20.0	33.5
4	4.1	4.1	3.9	56.3	56.3	72.9	52.2	52.2	69.0	53.3	53.3	70.5	49.2	49.2	66.6	51.8	51.8	64.8	48.8	48.8	63.1	23.0	23.0	33.5
8	5.8	5.8	5.5	51.8	51.8	68.3	46.0	46.0	62.7	48.8	48.8	65.9	43.0	43.0	60.4	45.7	45.7	58.9	42.7	42.7	57.2	24.5	24.5	36.6
10	6.5	6.5	6.2	50.3	50.3	66.7	43.8	43.8	60.6	47.3	47.3	64.2	40.8	40.8	58.1	43.8	43.8	57.0	40.8	40.8	55.3	25.0	25.0	36.7
16	8.2	8.2	7.8	47.2	47.2	63.6	39.0	39.0	55.8	44.2	44.2	61.2	36.0	36.0	53.4	39.7	39.7	52.9	36.7	36.7	51.1	25.0	25.0	38.5
20	9.3	9.3	8.7	45.8	45.8	62.0	36.5	36.5	53.2	42.8	42.8	59.5	33.5	33.5	50.8	37.8	37.8	51.0	34.8	34.8	49.2	25.0	25.0	38.8
25	10.4	10.4	9.8	44.3	44.3	60.3	33.9	33.9	50.5	41.3	41.3	57.9	30.9	30.9	48.2	35.8	35.8	48.9	32.8	32.8	47.2	24.3	24.3	39.4
31.25	11.7	11.7	11.0	42.9	42.9	58.9	31.2	31.2	47.9	39.9	39.9	56.6	28.2	28.2	45.7	33.9	33.9	47.0	30.9	30.9	45.2	23.6	23.6	39.8
62.5	17.0	17.0	15.6	38.4	38.4	54.2	21.4	21.4	38.6	35.4	35.4	51.9	18.4	18.4	36.2	27.9	27.9	40.8	24.9	24.9	39.0	21.5	21.5	34.7
100	22.0	22.0	20.0	35.3	35.3	50.9	13.3	13.3	30.9	32.3	32.3	48.6	10.3	10.3	28.6	23.8	23.8	36.9	20.8	20.8	35.1	20.1	20.1	30.9
155	28.1		25.1	32.4		47.8	4.4		22.7	29.4		45.3	1.4		20.2	20.0		33.1	17.0		31.3	18.8		28.3
200	32.4		28.8	30.8		45.6	-1.6		16.8	27.8		43.3	-4.6		14.5	17.8		30.7	14.8		28.8	18.0		27.6
250			32.4			43.7			11.3			41.4			9.1			28.7			26.8			26.9
300			35.7			42.0			6.3			39.7			4.0			27.0			25.1			26.5
350			38.9			40.5			1.6			38.3			-0.6			25.2			23.3			25.6