

AL4RPV-50R



AL4RPV-50, HELIAX® Plenum Rated Air Dielectric Coaxial Cable, corrugated aluminum, 1/2 in, Red PVDF jacket

- This product is part of the CommScope Wired for Wireless® Solution

Product Classification

Brand	HELIAX®
Product Series	AL4-50
Product Type	Air coaxial cable

Construction Materials

Jacket Material	PVDF
Dielectric Material	PE spline
Flexibility	Standard
Inner Conductor Material	Copper-clad aluminum wire
Jacket Color	Red
Outer Conductor Material	Corrugated aluminum

Dimensions

Nominal Size	1/2 in
Cable Weight	0.21 kg/m 0.14 lb/ft
Diameter Over Jacket	15.748 mm 0.620 in
Inner Conductor OD	4.5720 mm 0.1800 in
Outer Conductor OD	14.046 mm 0.553 in

Electrical Specifications

Cable Impedance	50 ohm \pm 2 ohm
Capacitance	76.0 pF/m 23.0 pF/ft
dc Resistance, Inner Conductor	1.570 ohms/km 0.480 ohms/kft
dc Resistance, Outer Conductor	1.570 ohms/km 0.480 ohms/kft
dc Test Voltage	4000 V
Inductance	0.190 μ H/m 0.058 μ H/ft
Insulation Resistance	100000 Mohms•km
Jacket Spark Test Voltage (rms)	5000 V
Operating Frequency Band	1 – 6000 MHz
Peak Power	40.0 kW
Power Attenuation	2.325
Pulse Reflection	0.5%
Velocity	88 %

AL4RPV-50R

Environmental Specifications

Installation Temperature	-5 °C to +60 °C (+23 °F to +140 °F)
Operating Temperature	-20 °C to +85 °C (-4 °F to +185 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +185 °F)

General Specifications

Ordering Note	CommScope® standard product (Global)
----------------------	--------------------------------------

Mechanical Specifications

Bending Moment	6.8 N-m 5.0 ft lb
Fire Retardancy Test Method	NFPA 262/CATVP/CMP
Flat Plate Crush Strength	1.4 kg/mm 80.0 lb/in
Minimum Bend Radius, Multiple Bends	127.00 mm 5.00 in
Minimum Bend Radius, Single Bend	64.00 mm 2.50 in
Number of Bends, minimum	15
Tensile Strength	79 kg 175 lb

Note

Performance Note	Values typical, unless otherwise stated
-------------------------	---

Standard Conditions

Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F
Average Power, Inner Conductor Temperature	100 °C 212 °F

Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
700–894 MHz	1.13	24.30
806–960 MHz	1.13	24.30
1700–2200 MHz	1.13	24.30

AL4RPV-50R

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
0.5	0.152	0.046	40.00
1	0.216	0.066	35.37
1.5	0.264	0.081	28.84
2	0.306	0.093	24.95
10	0.691	0.211	11.04
20	0.985	0.3	7.75
30	1.213	0.37	6.29
50	1.581	0.482	4.83
85	2.087	0.636	3.66
88	2.126	0.648	3.59
100	2.274	0.693	3.35
108	2.368	0.722	3.22
150	2.821	0.86	2.70
174	3.054	0.931	2.50
200	3.292	1.003	2.32
204	3.327	1.014	2.29
300	4.104	1.251	1.86
400	4.808	1.466	1.59
450	5.134	1.565	1.49
460	5.197	1.584	1.47
460	5.197	1.584	1.47
500	5.445	1.659	1.40
512	5.517	1.682	1.38
600	6.032	1.839	1.26
700	6.583	2.007	1.16
800	7.105	2.166	1.07
824	7.227	2.203	1.06
894	7.574	2.308	1.01
960	7.892	2.405	0.97
1000	8.081	2.463	0.94
1218	9.068	2.764	0.84
1250	9.207	2.806	0.83
1500	10.256	3.126	0.74
1700	11.053	3.369	0.69
1794	11.416	3.48	0.67
1800	11.439	3.487	0.67
2000	12.192	3.716	0.63
2100	12.559	3.828	0.61
2200	12.92	3.938	0.59
2300	13.276	4.046	0.57
2500	13.975	4.259	0.55
2700	14.656	4.467	0.52
3000	15.649	4.77	0.49
3400	16.928	5.159	0.45
3600	17.551	5.349	0.43

AL4RPV-50R

3700	17.859	5.443	0.43
3800	18.164	5.536	0.42
3900	18.467	5.628	0.41
4000	18.768	5.72	0.41
4100	19.066	5.811	0.40
4200	19.363	5.902	0.39
4300	19.658	5.991	0.39
4400	19.951	6.081	0.38
4500	20.241	6.169	0.38
4600	20.531	6.257	0.37
4700	20.818	6.345	0.37
4800	21.104	6.432	0.36
4900	21.388	6.519	0.36
5000	21.671	6.605	0.35
6000	24.42	7.443	0.31

* Values typical, guaranteed within 5%

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ETL Certification	CATVP/CMP
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
c(ETL)us Certification	CATVP/CMP

