

### Fiber Optic Outside Plant 96 Fiber, Loose Tube, Multi-tube Cable with Corrugated Steel Armoring, OM3, HDPE

- Designed for use in backbone cabling, campus site cabling, outdoor ducts or direct burial cabling applications
- Designed with a gel filled loose tube construction to ensure protection against moisture ingress

### Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber OSP cable
<b>Regional Availability</b>	Asia   EMEA


### Standards And Qualifications

<b>Cable Qualification Standards</b>	Telcordia GR-20-CORE
--------------------------------------	----------------------

### Optical Specifications, Wavelength Specific

<b>Standards Compliance</b>	TIA-492CAAB (OS2)   ANSI/TIA-568.C.3
-----------------------------	--------------------------------------

### Representative Image



## General Specifications

<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled
<b>Strength Members</b>	Central fiber reinforced polymer (FRP) rod

## Construction Materials

<b>Jacket Material</b>	High density polyethylene (HDPE)
<b>Total Fiber Count</b>	96
<b>Armor Type</b>	Corrugated steel
<b>Fiber Type</b>	OM3
<b>Fibers per Subunit, quantity</b>	12
<b>Jacket Color</b>	Black

## Dimensions

<b>Cable Length</b>	2000 m   6562 ft
<b>Cable Weight</b>	276.0 kg/km
<b>Diameter Over Jacket</b>	15.50 mm   0.61 in
<b>Filler, quantity</b>	0

## Physical Specifications

<b>Cable Crush Resistance, maximum</b>	44 N/mm
<b>Tensile Load, short term, maximum</b>	3000 N   674 lbf

## Environmental Specifications

<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
------------------------------	-------------------------------------

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable