

# LNXX-MNT-M

Side-By-Side Mounting Kit for 2.4 - 4.5 inch (60 – 115 mm) OD round members. The kit is used with the LNXX-MNT and is the middle mounting bracket when the antennas have three mounting points.

- For LNX 65° models that are 8 feet, the LNXX-MNT-M is used for a center mount along with the LNXX-MNT

**This product will be discontinued on: March 27, 2020**

**Replaced By**

BSAMNT-SBS-1-2      Side-By-Side Mounting Kit to mount two antennas on a pipe with 2.375 - 4.5 inch (60 – 115 mm) diameter

## General Specifications

<b>Application</b>	Outdoor
<b>Includes</b>	Brackets   Hardware
<b>Package Quantity</b>	1

## Mechanical Specifications

<b>Color</b>	Silver
<b>Material Type</b>	Galvanized steel

## Dimensions

<b>Compatible Diameter, maximum</b>	115.0 mm   4.5 in
<b>Compatible Diameter, minimum</b>	60.0 mm   2.4 in
<b>Net Weight</b>	7.3 kg   16.0 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)



## Included Products

BSAMNT-MH — Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

# BSAMNT-MH

---



Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

## General Specifications

<b>Application</b>	Outdoor
<b>Includes</b>	Brackets   Hardware
<b>Package Quantity</b>	1

## Mechanical Specifications

<b>Color</b>	Silver
<b>Material Type</b>	Galvanized steel

## Dimensions

<b>Compatible Diameter, maximum</b>	115.0 mm   4.5 in
<b>Compatible Diameter, minimum</b>	60.0 mm   2.4 in
<b>Net Weight</b>	4.5 kg   9.9 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)

