

## SnapStak® Hanger for 1-5/8 in coaxial cable



### Product Classification

|                     |            |
|---------------------|------------|
| <b>Brand</b>        | SnapStak®  |
| <b>Product Type</b> | Hanger kit |

### Dimensions

|                                     |                      |
|-------------------------------------|----------------------|
| <b>Nominal Size</b>                 | 1-5/8 in             |
| <b>Compatible Diameter, maximum</b> | 52.070 mm   2.050 in |
| <b>Compatible Diameter, minimum</b> | 48.260 mm   1.900 in |
| <b>Height</b>                       | 41.00 mm   1.61 in   |
| <b>Length</b>                       | 90.00 mm   3.54 in   |
| <b>Width</b>                        | 50.90 mm   2.00 in   |

### Electrical Specifications

|                           |        |
|---------------------------|--------|
| <b>DTF Effect</b>         | 0.1 dB |
| <b>Return Loss Effect</b> | 0.1 dB |

### Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -40 °C to +85 °C (-40 °F to +185 °F) |
|------------------------------|--------------------------------------|

### General Specifications

|                             |   |
|-----------------------------|---|
| <b>Hanger Type</b>          | Snap-in hanger  |
| <b>Cables per Hanger</b>    | 1   |
| <b>Color</b>                | Silver  |
| <b>Material Type</b>        | Stainless steel   |
| <b>Maximum Stack Height</b> | 2   |
| <b>Ordering Note</b>        | CommScope® standard product in Asia Pacific   CommScope® standard product in Mexico, Central America, and South America   CommScope® standard product in the United States and Canada |
| <b>Package Quantity</b>     | 10  |

## Mechanical Specifications

|  |                                  |
|--|----------------------------------|
| <b>Corrosion Resistance, minimum with no degradation</b> | ≥500 hours in salt spray chamber |
| <b>Mounting</b>  | 3/4 in drilled cable ladder      |
| <b>Vibration Survival</b>                                | ≥4 hours at resonant frequency   |
| <b>Environmental Strength Capability</b>                 | Double cable weight              |

## Packed Dimensions

|                        |                   |
|------------------------|-------------------|
| <b>Height</b>          | 22.0 cm   8.7 in  |
| <b>Length</b>          | 14.4 cm   5.7 in  |
| <b>Shipping Weight</b> | 0.60 kg   1.32 lb |
| <b>Width</b>           | 15.0 cm   5.9 in  |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



### \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power