



Lace-up Hoisting Grip for 5/8 in coaxial cable, elliptical waveguide 85, 90, 127, 132 and PWRT-608

## Product Classification

**Product Type** Hoisting grip

## Dimensions

**Nominal Size** 5/8 in  
**Grip Length, minimum** 508.00 mm | 20.00 in  
**Leader Length, minimum** 152.40 mm | 6.00 in

## Electrical Specifications

**DTF Effect** 0.1 dB  
**Return Loss Effect** 0.1 dB

## General Specifications

**Hoisting Grip Type** Lace-up hoisting grip  
**Attachment Spacing Intervals** 61 m | 200 ft  
**Material Type** Stainless steel  
**Ordering Note** CommScope® non-standard product  
**Package Quantity** 1  
**Support Clamp** Not included  
**Tool Type** Hoisting grip

## Mechanical Specifications

**Pull Load Capacity** 500 lb

## Packed Dimensions

**Height** 5.7 cm | 2.3 in  
**Length** 23.5 cm | 9.3 in  
**Width** 23.5 cm | 9.3 in  
**Shipping Weight** 0.30 kg | 0.66 lb

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)

